


Date: _____
 In hands date of project: _____
 Project name/Number: _____
 Name of distributor: _____
 Client #: _____
 Name of end user: _____



Nominal length : 46 in. (1 168 mm) Dia. : 5/8 in. (16 mm)

ORDERING INFORMATION

Order code: 65480
 Description: LED/T5/S2/25.5W/840/46/STD/SMX
 UPC: 69549654808
 Case quantity: 25



PERFORMANCE DATA

Shape: T5
 Base: G5
 Watts (W): 25.5
 Starting method: Program Start
 Lamp voltage (VAC): 120 V-277 V / 347 V
 Color temperature (K)**: 4 000
 Average life (L70 hours): 50 000
 Initial Lumens (lm)*: 3 100
 Initial lumens per watt (lm/W): 122
 CRI: >80
 Beam angle (°): >240
 Coating: PET Polyethylene Terephthalate
 Operating temperature range: -20°C / -4°F to 45°C / 113°F
 DLC Listed: DLC Standard

*Initial lumens range: +/- 10 %

**Typical colour temperature range: +/- 5 %



CONFORMS TO NSF/ANSI 2

Please refer to the ballast compatibility list to confirm lamp compatibility with the existing luminaire.

CAUTIONS

THIS LAMP OPERATES ON PROGRAM START ELECTRONIC BALLASTS.
 Direct replacement for 54 watts lamps only. Risk of fire. Do not install this lamp in a pre-heat luminaire. Risk of electric shock – for use in damp locations.
 Not for use in totally enclosed luminaires.

Qty	Description	Price

I accept the specifications of the lamp configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment and representative of relative performance.
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

May 3, 2016

