Technical Information Bulletin

LED T8

Dia.: 1 in. (26 mm)

MOL: 35 3/4 in. (908.8 mm)

Date:	 _	
In hands date of project:		
Project name/Number:		
Name of distributor:		
Client #:	 	
Name of end user:		
	•	

ORDERING INFORMATION

Order code: 66157

Description: LED/T8/12W/840/36/BYP/120-277/ND/STD

UPC: 69549661578

Case quantity: 25

PERFORMANCE DATA

Shape: T8 Base: G13

Install method: Ballast bypass

Watts (W): 12

Lamp voltage (VAC): 120 V - 277 V

Color temperature (K)**: 4 000
Initial Lumens (Im)*: 1 450
Initial lumens per watt (Im/W): 121
Average life (L70 hours): 50 000
CRI: 82
Dimmable: No

Operating temperature range: -20°C / -4°F to 45°C / 113°F

*Initial lumens range: +/- 10 % **Typical colour temperature range: +/- 5 %















^{*}This product complies with UL1598C Standard for LED luminaire Retrofit kits. Not suitable for hazardous location.

CAUTIONS

Only for ballast bypass installation in 120-277V applications. Not for use in 347V direct line voltage applications.

Direct replacement for 21 & 25 watts T8 lamps only. Do not use with dimmers. Not for emergency lighting. Risk of electric shock – for use in damp locations.

Qty	Description	Price
I accept the s	specifications of the lamp configuration mentio	ned above.
Name:	<u> </u>	
Company:		
Signature:		Date:

STANDARD®