

Technical Information Bulletin

CHOICE LED Lamps



Date: _____ Name of distributor: _____
In hands date of project: _____ Client #: _____
Project name/Number: _____ Name of end user: _____

ORDERING INFORMATION


Order code: 66279
Description: P20/8W/27K/25/CHOICE/STD
UPC: 69549662797
Case quantity: 12

PERFORMANCE DATA

Shape: PAR20
Base: E26
Watts(W): 8
Volts (VAC): 120
Colour temperature (K)**: 2 700
Life L70 (hrs): 15 000
Initial lumens (lm)*: 581
Initial lumens per watt (lm/W): 73
CRI: 92
Beam angle (°): 25
CBCP: 1 708
Power factor: 0.91
Operating temperature range: -20 °C to 40 °C (-4 °F to 104 °F)
Traditional equivalent (W): 50

*Initial lumens range: +/- 10 %

**Typical colour temperature range: +/- 10 %



COMPATIBLE DIMMERS

Lutron PD5NE, RRD6NA, DVRP253, SELV-300P



CAUTIONS

- Turn power off before inspection, installation, or removal.
- Not for use in totally enclosed luminaires.
- Suitable for use in damp locations.
- Do not open – no user serviceable parts inside.
- Use only on 120 VAC, 60Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers.
- For complete dimmer and warranty information visit www.standardpro.com.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
Company: _____
Signature: _____

Date: _____

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.
Data is based upon tests performed in a controlled environment and representative of relative performance.
Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

September 30, 2019