

Technical Information Bulletin

LED Linear Tubes



Date: _____ Name of distributor: _____
In hands date of project: _____ Client #: _____
Project name/Number: _____ Name of end user: _____

ORDERING INFORMATION

Order code: 66992
Description: T5/13W/835/46/STD
UPC: 69549669925
Case quantity: 25
DLC Unique ID: PLEG7N4CILNR



Nominal length : 46 in. (1 168 mm) Dia. : 3/4 in. (19.5 mm)

PHYSICAL DATA

Shape: T5
Base: G5
Material: Glass

PERFORMANCE DATA

Bare lamp watts (W): 13
System watts (W): 16
Volts (VAC): 120 -277/347
Colour temperature (K)¹: 3 500
Initial Lumens (lm)²: 1 800
Initial lumens per watt (lm/W): 112
Life L70 (hrs): 50 000
CRI: 82
Starting method: Program Start
Operating temperature range: -25°C to 45°F (-13°C to 113°F)

¹ Typical colour temperature range: +/- 5 %

² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %



Please refer to the ballast compatibility list to confirm lamp compatibility with the existing luminaire.

ADDITIONAL INFORMATION

THIS LAMP OPERATES ON PROGRAM START ELECTRONIC BALLASTS.
Direct replacement for 28 watts lamps only.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____

Company: _____

Signature: _____

Date: _____

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.
Data is based upon tests performed in a controlled environment and representative of relative performance.
Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.