



Southwire™

TOOLS & EQUIPMENT

LED STRING LIGHT

acme 
construction supply co., inc.

Southwire's LED String Light is the perfect LED solution for any jobsite application. Available in 50ft and 100ft lengths, this light features LEDs on the top and bottom of the module giving full jobsite coverage. These lights are also IP65 and outdoor rated to protect against the ingress of water and dust. Also, Daisy chain up to 10 strings of the 100' model and 20 strings of the model 50' for longer lengths.

LEDS ON TOP AND BOTTOM OF THE LIGHT PROVIDE UPLIGHT AND DOWNLIGHT COVERAGE.

IP65 RATED

DAISY CHAIN UP TO 10 STRINGS OF THE 100' MODEL AND 20 STRINGS OF THE MODEL 50' FOR LONGER LENGTHS.

MAINTENANCE FREE

UL 1088, FCC/ICES





Southwire™

TOOLS & EQUIPMENT



LED STRING LIGHT

FEATURES & BENEFITS

- 7.8W per module delivers 700 lumens downlight and 100 lumen uplight
- Daisy chain 10 strings with the 100' version and 20 strings with the 50' version
- IP65 Rating helps to protect from dust and water
- Robust, rugged LED lighting design
- Zero maintenance with no need to change bulbs



SPECIFICATIONS

Product#	Length	Wattage	Total Lumens	# of strings daisy chained	Input Voltage	CCT	CRI	Cord Type
7164SW	50'	39W	4000	20	120V	5000±10%	>75	14/3 SJTW
7165SW	100'	78W	8000	10	120V	5000±10%	>75	14/3 SJTW

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-SWTOOLS | 1-855-798-6657 | SOUTHWIRETOOLS.COM

©2017 Southwire Company, LLC. All rights reserved. ™Trademark of Southwire Company, LLC.