

# Technical Information Bulletin

## LED Linear Tubes



Date: \_\_\_\_\_ Name of distributor: \_\_\_\_\_  
 In hands date of project: \_\_\_\_\_ Client #: \_\_\_\_\_  
 Project name/Number: \_\_\_\_\_ Name of end user: \_\_\_\_\_

### ORDERING INFORMATION

**Order code:** 67001  
**Description:** LED/T8/S4/11W/835/36/STD/SMX  
**UPC:** 69549670013  
**Case quantity:** 25  
**DLC Unique ID:** PLZINA2749ZX



### PHYSICAL DATA

**Shape:** T8  
**Base:** G13  
**Material:** Glass and PET Polyethylene Terephthalate



### PERFORMANCE DATA

**Bare Lamp Watts (W):** 11  
**Volts (VAC):** 120 -277/347  
**Colour temperature (K)<sup>1</sup>:** 3 500  
**Life L70 (hrs):** 50 000  
**CRI:** 82  
**Starting method:** Instant, Rapid & Program Start  
**Operating temperature range:** -25°C to 45°F (-13°C to 113°F)

Order code	Average System Watts (W)			Initial Lumens (lm) <sup>2</sup>		
	LBF	NBF	HBFS <sup>3</sup>	LBF	NBF	HBFS <sup>3</sup>
67001	12	14	20	1 450	1 600	2 200

<sup>1</sup> Typical colour temperature range: +/- 5 %  
<sup>2</sup> Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %  
<sup>3</sup> LBF= Low ballast factor, NBF= Normal ballast factor, HBF= High ballast factor



Please refer to the ballast compatibility list to confirm lamp compatibility with the existing luminaire.

### ADDITIONAL INFORMATION

THIS LAMP OPERATES ON INSTANT START, RAPID START AND MANY PROGRAM START ELECTRONIC BALLASTS.  
 Direct replacement for 25 watts lamps only.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: \_\_\_\_\_  
 Company: \_\_\_\_\_  
 Signature: \_\_\_\_\_

Date: \_\_\_\_\_

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.  
 Data is based upon tests performed in a controlled environment and representative of relative performance.  
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.