

FEATURES & SPECIFICATIONS

INTENDED USE — The 4" Wafer-Thin LED recessed downlight with remote driver box combines high quality light output and efficiency while eliminating the need for a recessed housing. The innovative, slim design allows for easy retrofit, remodel or new construction installation from below the ceiling. The Wafer downlight provides general illumination in residential and commercial applications including multifamily and hospitality. Ideal for use in living and dining areas, bedrooms, closets, hallways, bathrooms, showers, kitchens, basements, soffits, entryways and porches. The Wafer LED downlight is wet location listed - making it ideal for use in a breadth of outdoor residential, hospitality, commercial and multifamily applications.

CONSTRUCTION — Die cast aluminum mounting frame with integral polycarbonate flange provides passive thermal cooling achieving L70 at 50,000 hours. Non-conductive dead-front trim design suitable for a wide range of applications and codes requiring a non-conductive lens assembly. IC rated driver and fixture - approved for direct contact with insulation. FT4 plenum rated cable connector to connect from module to remote driver box. Isolated driver integrated inside steel remote box with four 7/8" knockouts with slots for pryout. Suitable for pulling wires with the 12 cubic-inch wiring compartment to accommodate up to (6) 14 gauge insulated conductors; making the Wafer LED Downlights much easier to wire in 2in/2out (plus ground) daisy-chain applications and contractor friendly. Wire nuts included.

INSTALLATION — Ideal for shallow ceiling plenum; no housing required. Steel spring clip for easy installation. 4" cut out template provided to ensure correct sized hole is cut into ceiling for proper installation of the trim. Size of hole should not exceed 4 1/4 inches for this product. Suitable for installation in t-grid and drop ceiling applications with the WF8643 Pan. 3" plenum space required for installation of the remote driver box.

OPTICS — Edge-lit LED technology uses light guided plate to distribute light. Polycarbonate lens provides even illumination throughout the space. Utilized 3000K and 4000K color temperature LEDs binned within 3-step MacAdam ellipse, 90 CRI.

ELECTRICAL — Connect directly to 120V power supply via provided UL recognized driver. High efficient driver with power factor > 0.9. Ambient operating temperature: $-40^{\circ}F(-40^{\circ}C)$ to $+104^{\circ}F(+40^{\circ}C)$. Dimming down to 10% (See page 2 for recommended dimmers).

LISTINGS — CSA certified to US and Canadian safety standards. ENERGY STAR® certified product. Wet location. Air Tight certified in accordance with ASTM E283-2004. NOM Certified. Can be use for State of California Title 24 high efficacy LED compliance under JA8, reference Modernized Appliance Efficiency Database System (MAEDBS) for 2016 JA8 High Efficacy Lighting.

WARRANTY — 5-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/support/warranty/terms-and-conditions

Note: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25 °C. Specifications subject to change without notice. Catalog Number

Notes

Туре

Wafer Static LED Recessed Downlight


WF4E 4" LED Module

IC/Non-IC New Construction/Remodel





Specifications								
Aperture:	3.2 (9.06)							
Ceiling opening:	4 (10.40)							
Overlap trim:	4.7 (12)							
Height:	0.4 (1.11)							
Weight	0.8lbs							
All dimensions are inches (centimeters) unless otherwise indicated.								



Only compatible with single layer sheet rock.

Example: WF4E LED 30K 90CRI MW

ORD	ERING IN	IFORM	ΔΤΙΟΝ


WF4E						
Series	Lamp	CCT/W/Lumens ¹	CRI	Finish	Package Quantity	
WF4E 4" wafer-thin LED downlight	LED LED	30K 3000K/8.1W/580L 40K 4000K/8.1W/600L	90CRI 90 CRI	MW Matte White	CP6 6 units per carton ²	



PHOTOMETRICS

Distribution Curve Distribution Data		ta	Output	Data	Coefficient of Utilization	Illuminance Data at 30″ Above Floor for a Single Luminaire		
4E LED 30K 90CRI, 3000 Polar Candela Distributi	<i>i</i> 1	s: 8.14, de	livered lumen:	s: 578.5, LM/W	=71, test no. ISF 193258			
180° 170° 18	130° 120°	RCC %: RW %:	80 70 50 30 0	ATTON - ZONAL CAV 70 70 50 30 0	EFFECTIVE FLOOR CAVITY REFLECTANCE: 209 50 30 10 0 50 30 20 50 30 20 0	0-30 162.1 28% 0-40 263.2 45.5%		
73 37	110° 100° 90°		1.09 1.04 1.00 .96 .99 .91 .84 .78 .90 .80 .71 .65	1.06 1.02 .98 .84 .96 .89 .82 .71 .88 .78 .70 .60	85 .80 .75 .82 .77 .73 .79 .75 .72 .7 .75 .68 .63 .72 .67 .62 .70 .65 .61 .5	0-60 457.3 79.1% 60-90 121.2 20.9% 0-90 578.5 100%		
37 73 10	80° 70° 60°	4 5 6 7	.83 .71 .62 .55 .76 .63 .54 .47 .70 .57 .48 .41 .65 .52 .43 .37	.74 .62 .53 .45 .68 .56 .47 .40 .63 .51 .42 .36	.60 .52 .47 .58 .51 .46 .56 .50 .46 .44 .54 .47 .41 .52 .46 .41 .51 .45 .40 .33 .49 .42 .36 .48 .41 .36 .46 .40 .36 .34	3 3 4		
47 83 20 VA: 0° 10° 21	50°	8 9 10	.61 .47 .39 .33 .57 .43 .35 .29 .53 .40 .32 .27	.55 .43 .35 .29	.41 .34 .29 .40 .34 .29 .39 .33 .29 .2	7		

WF4E LED 40K 90CRI, 4000 K LEDs, input watts: 8.22, delivered lumens: 598.6, LM/W=72.8, test no. ISF 193597



COEFFI	CIEN	TS O	F UT	ILIZ/	TION	I - Z(DNAL	. CAV	ΙΤΥ Μ	ETH	OD								ZONAL	. LUMEN	SUMMARY
	EFFECTIVE FLOOR CAVITY REFLECTANCE: 20%										: 20%	ZONE I	UMENS 9	% LUMINAIRE							
RCC %:		8	0			- 7	0			<i>50</i>			30			10		0	0-30	171.3	28.6%
RW %:	70	<u>50</u>	<u>30</u>	0	70	<u>50</u>	<u>30</u>	0	50	<u>30</u>	20	50	30	20	50	30	20	0	0-40	277.7	46.4%
RCR: 0	1.19	1.19	1.19	1.19	1.16	1.16	1.16	1.00	1.11	1.11	1.11	1.06	1.06	1.06	1.02	1.02	1.02	1.00	0-60	479.7	80.1%
1	1.09	1.04	1.00	.96	1.06	1.02	.98	.85	.98	.95	.92	.94	.91	.89	.90	.88	.86	.84	60-90	119	19.9%
2	.99	.91	.84	.79	.97	.89	.83	.72	.86	.80	.76	.82	.78	.74	.79	.76	.73	.70	70-100	49	8.2%
3	.91	.80	.72	.66	.88	.79	.71	.61	.76	.69	.64	.73	.67	.63	.70	.66	.62	.60	90-120		
4	.83	.71	.62	.56	.81	.70	.62	.53	.67	.60	.55	.65	.59	.54	.63	.57	.53	.51		0	0%
5	.76	.64	.55	.48	.74	.62	.54	.46	.60	.53	.47	.58	.52	.47	.57	.51	.46	.44	0-90	598.6	100%
6	.71	.57	.48	.42	.69	.56	.48	.41	.55	.47	.42	.53	.46	.41	.51	.45	.41	.39	90-180	0	0%
7	.65	.52	.43	.37	.64	.51	.43	.36	.50	.42	.37	.48	.42	.37	.47	.41	.36	.34	0-180	598.6	100%
8	.61	.48	.39	.33	.59	.47	.39	.32	.46	.38	.33	.44	.38	.33	.43	.37	.33	.31			
9	.57	.44	.35	.30	.56	.43	.35	.29	.42	.35	.30	.41	.34	.30	.40	.34	.29	.28			
10	.53	.40	.32	.27	.52	.40	.32	.27	.39	.32	.27	.38	.31	.27	.37	.31	.27	.25			

ENERGY DATA & DIMMING CAPABILITY

4" ENERGY DATA							
Color Temperature	3000K	4000K					
Lumens	580	600					
CRI	90	90					
Lumens/Watt	71.6	74.1					
Min. starting temperature	-40°C (-40°F)	-40°C (-40°F)					
EMI/RFI	FCC Title 47 CFR, Part 15, Class B	FCC Title 47 CFR, Part 15, Class B					
Sound rating	Class A Standards	Class A Standards					
Input voltage	120V	120V					
Min. power factor	.99	.99					
Input frequency	60 Hz	60 Hz					
Rated wattage	8.1W	8.1W					
Input power	8.1W	8.1W					
Input current	0.09A	0.09A					

COMPATIBLE DIMMERS								
Lutron	Leviton	Cooper	Belkin					
D-603P-WH	6672	DLC03-W	Wemo w/Wifi					
DVELV-300P	DW6HD							
300P SELV	DZ6HD							
DV-600PR	6674 - LED/INC mode							
NTELV-300P	RPI06-10Z							
PD-6WCL	IPL06 -10Z LED/INC mode							
MACL-153MH	IPI06-1LZ							
MAELV-600-WH	IPM10-1LZ							
LECL-153PH-WHB								
CTCL-150H								
PD-5NE-WH								
Caseta Wireless PD-6WCL								