# Technical Information Bulletin CHOICE LED Lamps



Date:	Name of distributor:
In hands date of project:	Client #:
Project name/Number:	Name of end user:

#### **ORDERING INFORMATION**

Order code:	66306
Description:	GU10/6.5W/30K/40/CHOICE/STD
UPC:	69549663060
Case quantity:	24



# PERFORMANCE DATA

Shape:	GU10
Base:	GU10
Watts(W):	6.5
Volts (VAC):	120
Colour temperature (K)**:	3 000
Life L70 (hrs):	15 000
Initial lumens (lm)*:	500
Initial lumens per watt (lm/W):	77
CRI:	80
Beam angle (°):	40
CBCP:	778
Power factor:	0.9
Operating temperature range:	-20 °C to 40 °C (-4 °F to 104 °F)
Traditional equivalent (W):	50

\*Initial lumens range: +/- 10 % \*\*Typical colour temperature range: +/- 10 %



### CAUTIONS

- Turn power off before inspection, installation, or removal.
- Not for use in totally enclosed luminaires.
- Suitable for use in damp locations.
   Do not open pouser serviceable part
- Do not open no user serviceable parts inside.
  Use only on 120 VAC, 60Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers.
- For complete dimmer and warranty information visit www.standardpro.com.

Qty	Description	Price
I accept the spec	cifications of the luminaire configuration mentione	d above.
Name:		
Company:		
Signature:		Date:

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

## **COMPATIBLE DIMMERS**

Cooper	SLC03P
Leviton	6615, DSL06-1LZ, DSM10-1LZ, IPE04- 1LZ
Lutron	AYCL-253P, DVCL-253P, DVELV-300P, MACL-153P, SELV-300P