

The image shows three Siemens HVAC units installed outdoors. They are cylindrical with a white top and a black wire mesh body. The units are positioned in a row, with the one in the foreground being the most prominent. The background shows a light-colored wall and some greenery.

SIEMENS

"Tweener" Ground Fault Circuit Interrupter (GFCI)

Expanded GFCI line for complete home safety

With the extension of the National Electrical Code 2020 to protect more areas of the home, Siemens has expanded our GFCI product line, continuing to provide complete home safety for our customers. The NEC 2020 Article 210.8(F) extends GFCI protection to circuits feeding HVAC units and other modern-life applications.


In the example of HVAC, the unit is supplied by a single-phase 240V branch circuit, rated 50A or less. GFCI protection is required for the outlet serving each unit. Siemens now offers the "in-between" amperage circuit breakers to its 2-pole GFCI portfolio for such a requirement.

Features

- Available in 2-pole 25, 35 and 45A ratings
- Available in 10kAIC rating
- Includes a Self-Test as required by UL943 as an added safety feature.
- Suitable for a variety of construction applications: HVAC, spas, hot tubs, kitchens, bathrooms, etc.
- Resists false tripping (shielded to prevent RF interference)
- Standard 1 inch per pole format with plug-in design
- UL Listed and CSA Certified
- Provides Class A GFCI protection
- HACR and SWD rated

"Tweener" Ground Fault Circuit Interrupters

Catalog Number	Poles	Ampere Rating	Interrupting Rating
QF225A	2	25	10kAIC
QF235A	2	35	10kAIC
QF245A	2	45	10kAIC



Published by
Siemens 2021

Siemens Industry, Inc.
3617 Parkway Ln.
Peachtree Corners, GA 30092

Siemens Technical Support: 1-800-333-7421
info.us@siemens.com

Printed in USA-CP
Order No. RPFL-GFCIT-0121
All Rights Reserved
© 2021, Siemens Industry, Inc.
usa.siemens.com/afci

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.