


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL

PANDUIT * PART NO.	ADHESIVE BACKING	MAX. BUNDLE ~DIAMETER inches (mm)	WEIGHT  b(g)/100 pcs.		
MACC62-A	RUBBER				
MACC62-AV	HIGH BOND ACRYLIC	0.62 (16)	0.90 (408)		







- PRESSURE SENSITIVE FOAM TAPE-0.05 (1.3) THICK WITH PROTECTIVE LINER.

## NOTES:

- \* 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATIONS FOR PACKAGE SIZE.
  - 2) TO APPLY MOUNT: a) REMOVE PROTECTIVE LINER,
    - 6) PLACE IN DESIRED LOCATION,
    - c) APPLY PRESSURE TO MOUNT.
  - 3) MATERIAL:

G-90 PRE-GALVANIZED COMMERCIAL GRADE LOW CARBON STEEL, PER ASTM A 653 STEEL SHEET, ZINC COATED (GALVANIZED) BY THE HOT DIP PROCESS. (DIMENSIONS IN PARENTHESES ARE IN METRIC.)

G03597GV\_DC\_GB02391R/00B



TINLEY PARK, ILLINOIS

MACC62-A & MACC62-AV METAL ADHESIVE CORD CLIP

00B	11-6-09	TMSA	SMY			KW			UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED.		
2	2/19/03	JAD		UPDATED MATERIAL DESIGNATION, ADD NOTE 3	TED MATERIAL DESIGNATION.   CROSSOLD		.1(2.5) (.XXX) ± 0.020(.5)	ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.					
١.						<del> </del>	ļ				:03(1:3)/MOLEG E G	IN INCHES, INTHU ANGLE PROJE	CITON.
1	11-26-01	LGG		ADDED DIMS AND REF DIMS	GB02391R	1				LGG	MATILE	NOT TO SC	ALE
R	7-30-01	LGG		DRAWING RELEASED REPLACED SS-22006	GB02391R	R				DATE		DRAWING NO.	OWG
					00020011					7/30/01	SEE NOTE 3		,
REV	DATE	ву	CHK	DESCRIPTION	ECN -	R	CUST	SUP		CHK.D K(N		GB02391R	Α
							L	<u> </u>	11	,			SIZE