						2				1				
		THIS CO	PY IS	5 PRO	VIDED	ON A RESTRICTED BASIS AND IS NOT TO BE U	Ged in any w	AY DETRI	MENTAL	TO THE I	NTERESTS	OF PANDUIT CORP.		
				$\wedge$	.)	$\bigcirc \land$		I TEN NO.	(PCS.)	PART NO.		DESCRIPTION		
								1 2	1	GMSDCOM	F	PANDUIT SCREWDRIVER	<u> </u>	
									1 PSL-BX		CARRYING CASE RED NON-CONDUCTIVE PADLOCK		-	
					,		$\frown$	3	3	PSL-8 PSL-MLD		LTIPLE LOCKOUT DEVICE		
								5	2	PSL-WS		ALL SWITCH LOCKOUTS		
				C	$^{\prime}$ $^{\prime}$		0	6	2	PSL-CBNT	"NO TOOI	L" CIRCUIT BREAKER LOCKOUT		
					1			7	2	PSL-P		DEVICE PLUG LOCKOUT DEVICE		
								8	1	PSL-V6A		LVE LOCKOUT -5.0" [127 mm]	]	
								, 9	1	PSL-V2A	GATE VA	LVE LOCKOUT -2.5" [64 mm]		
				$\bigcirc$			(10)	8 10	1	PSL-BV2		LVE LOCKOUT - 3.0" [76 mm]		
_												AC Cord Lockout Device, R		
B					$\backslash$		<u>\</u>	12	10	PV1-44	DU NUT	OPERATE" MAINTENANCE TAGS	<u>B</u>	
							$\rightarrow$							
								$\square$						
								$\langle \rangle$						
						A call	000000	#/	1		1			
								V	◀─── 12.50 ──► ◀─ 7.50 ─►					
										[317.5	<u> </u>	[190.5]		
										REF.		REF.		
			DO NO <sup>.</sup>		REMOVE THIS TAG	G / / / /								
		Í 🧕 Ö	PERAT		t					/	$\neg $			
		0												
		M P M	AINTENAN Epartmei	CE			Ð				$\langle \rangle$			
	C UEPARTIWENT SEE OTHER SIDE (7)						<							
							·)							
		/		/	× 60		ДЪ		\					
					6			T			<u>PSL-E</u>	$\times$		
		(	12											
			$\bigcirc$						ΡL	ASTIC	LARR	YING CASE		
					. 🖊 . '		PMOUT							
				$\bigcirc$										
				$(\underline{6})$			~							
						(4)								
								TITLE				· · · · · · · · · · · · · · · · · · ·		
	8	3/3/2020	RVU	DJW	JHAC	REPLACED LATEST RECTANGLE MODEL TO CURRENT HEXAGON MODEL.	GAECN05588	PSL-KT-MROA				A		
A	7	4/21/17	RVU	DJW		UPDATE ALL ISO VIEWS WITH PSL-BX. UPDATE TABLE. REMOVE GMPSL-INMLD, AND GMPSL-INI, ITEM 14, & 15.	GAECN04106		MAINTENANCE LOCKOUT KIT					
	6	8/29/16 RVU SEWH JHAC REPLACE WITH PSL-CBNTWIP TO PSL-CBNT.					GAECN03608	ITEM REVISION	I NAME	CUS	STOMER DRA	AWING		
	5	6/17/14 RVU MJPF MSAD 7.25 WAS 5.0, 12.50 WAS 14.5, AND 7.50 WAS 6.5.				GAECN02088	IO0619CX/10							
	4	11/11/09	RVU			PSL-8 WAS PSL-3RED-LS. ADD LEADERS	5905	DATASET FILE		_DC_C10387/1	DJ		8	
	3		RVU			15 AND 16 FOR GMPSL-INMLD, AND PSL-IN1. PSL-PL1REDY ADDED.	5279	UNL	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]					
		12/10/07					5230	.X ± .XXX ± .XXX						
		9/13/06 RVU MISC. REVISION.				4659	.×× ±	.XX ± ANGLES ±						
						4033		-	THIF	D ANGLE				
	-			.200	DRAWN BY DAT	E Y		JECTION	C10387	SIZE				
	REV	DATE	ΒY	СНК	APR	DESCRIPTION	ECN	RVU	10/18/05	RVU	NTS		A	
				1	1	2		ı — İ						
							1						_	