



## KS26

by Burndy  
Catalog ID: KS26

Prop 65 Notice

Copper Split Bolt, Cu: 2 AWG-2/0 AWG (Str) (Run & Tap).

Features: UL467 Listed For Direct Burial Applications In Earth Or Concrete, Compact, High-Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Cracking And Corrosion, Conductor Type: Run And Tap: Solid Copperweld, Commercial Stranded And Solid Copper, Stranded Copperweld, Installation Torque: 385 IN-LB, Length: 1.94 IN, Cross Flats: 15 IN, Width: 0.82 IN

## Product Details

### General

Application	For Direct Burial Applications In Earth Or Concrete, Copper
Connector Type	Split Bolt
Installation Torque Recommended in-lb	385 in
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS, Compact
UPC	781810013281
UPC 12 Digit	7818100132811

### Dimensions

Dimension - B Length fraction	9/10 in
Dimension - B Length inch	.90 in
Dimension - Cross Flats inch	1.05 in
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.94
Dimension - Width fraction	41/50 in
Dimension - Width inch	0.82 in
Dimension - Width mm	21 mm
Width	0.82 in

### Conductor Related

Conductor - Copper Solid Run	3/0 AWG
Conductor - Copper Solid Run Range	2 AWG-2/0 AWG
Conductor - Copper Solid Tap	3/0 AWG
Conductor - Copper Solid Tap Range	14 AWG-2/0 AWG
Conductor - Copper Str Run	2 AWG;1 AWG;1/0 ;2/0 AWG

Conductor - Copper Str Run Range	2 STR - 2/0 STR
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	2 STR - 2/0 STR
Conductor - CopperWeld Solid Run	3/0
Conductor - CopperWeld Solid Run Range	3/0
Conductor - CopperWeld Solid Tap	3/0
Conductor - CopperWeld Solid Tap Range	3/0
Conductor - CopperWeld Str Run	7 #7
Conductor - CopperWeld Str Run Range	7 #7
Conductor - CopperWeld Str Tap	7 #7
Conductor - CopperWeld Str Tap Range	7 #7
Conductor - Rebar Size	3
Conductor - Rebar Size Range	3
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Run</li> <li>• CU C Str-Run</li> <li>• CU Weld C Solid-Run</li> <li>• CU Weld C Str-Run</li> <li>• CU C Str-Tap</li> <li>• CU Weld C Solid-Tap</li> <li>• CU Weld C Str-Tap</li> <li>• CU C Solid-Tap</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL 486A</li> <li>• UL486B</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>• UL 486A</li> <li>• UL486B</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)