

# YA27A3

by Burndy  
Catalog ID: YA27A3

Prop 65 Notice

Aluminum Compression Lug, 1 Hole w/o Inspection Window, 3/0 AWG, 1/2" Stud, Tin Plated.

Features: Type YA-A Aluminum Tin-Plated Compression HYLUG Terminals Are Dual-Rated And Designed For Use On Both Aluminum And Copper Conductors From #12 Solid Through 2000 KCMIL, They Are Designed For Heavy Duty Applications To 35 KV, YA-A Terminals Are Prefilled With PENETROX, And Assembled With Color-Coded End Caps, Available With One, Two, And Four-Hole NEMA Tongues, The Aluminum HYLUG Terminals Are Designed For A Permanent Trouble-Free Electrical Termination, Manufactured From High Conductivity, Wrought Aluminum With Heavy Duty Wall Thickness: Provides Maximum Conductivity, Low Resistance And Ductility For An Excellent Combination Of Electrical And Crimp Forming Properties, Electro-Tin Plated: Provides Durable Long Lasting Corrosion Resistance, Internally Bevelled Barrel: Provides Easy Cable Insertion, Meets UL486B 90 DEG C Requirements: Provides A Quality Electrical Dual Connection, Connector Is Clearly Marked With Wire Size, Die Index, Color-Code And The Proper Number And Location Of Crimps: Provides Easy Identification And Tooling Recommendation For A Proper Compression Which Forms A Homogeneous Mass Resulting In An Excellent Electrical Connection, Factory Prefilled With PENETROX Oxide Inhibiting Compound: Oxide Inhibiting Compound Contains Homogeneously Suspended Metallic Particles To Penetrate The Wires Oxides, Establish Electrical Continuity And Forms An Airtight Connection, Color-Coded End Caps Inserted In Barrel End: Prevents Foreign Materials From Entering And Contaminating The Connector Prior To Usage Plus Identifies The Proper Color-Coded Die For A Reliable Connection, UL Listed 90 DEG C, 600 V - 35 KV, Wire Strip Length: 1-1/2 IN, Temperature Rating: 90 DEG C, Finish: Electro-Tin Plated, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y39, Y750 Tool, U27ART Die, (2), Y46 Tool, U27ART Die With PUADP-1 Adapter, (2), Color Code: Ruby, Die Index: 467, Dieless Tools (number Of Crimps): Mechanical: MY29-3, MRC840AL Tool, (2), Hydraulic HYPRESS: Y644HS Tool, (1), Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (2)



## Product Details

### General

Application	For Aluminum And Copper Conductors
Color Code	Ruby
Connector Type	Terminal
Die Index	467
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	YA-A, Dual Rated

UPC	781810754108
UPC 12 Digit	7818107541088

## Dimensions

Dimension - B Length fraction	1-5/16 in
Dimension - B Length inch	1.31 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	1.37 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	83 mm
Dimension - Length Overall inch	3.27 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.76 in
Dimension - Pad Width inch	1.04 in
Dimension - Strip Length inch	1-1/2
Dimension - Stud Size inch	1/2
Dimension - Thread Size	1/2
Dimension - Z inch	0.74 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - AL Str Size	3/0 AWG
Conductor - AL Str Size Range	3/0 AWG
Conductor - Copper Str Size	3/0 AWG
Conductor - Copper Str Size Range	3/0 AWG

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)