

NEXTSPEED
Category 5e Component

Angled Patch Panel

Features

- 7 dB min NEXT Margin 1 -100 MHz over TIA and ISO Channel Specifications
- Qualified to 150% of 802.3bt PoE Current Level
- Continuous Third Party Verification Program

Ordering Information

Description	Color	Catalog Number	UPC
NEXTSPEED Category 5e Patch Panel, Angled, 48-Port, 2 Rack Unit	Black	HP5E48A	662620247137

Listings

TIA-568-C.2 Category 5e component
ISO/IEC 11801/60603-7-41 5e component
Third Party tested for TIA 568-C.2 requirements. Component/link/channel
ISO/IEC 11801 Class D
Mechanical: Verified to TIA-568-C.2
UL Listed 1863, UL 94 V-0 Flammability Rating ISO9001-2008 manufacturing process

Specifications

Nose Contact	Beryllium copper with precious metal plating with nickel under-plating
Rear IDC Contact	Phosphor bronze with 100 micro-inch lead free tin plating over nickel under plating
Panel Material	14 ga. Steel rolled-edge construction
Dimensions (W x H) Inch (mm)	19 (483) x 3.50 (89)
Mounting	Dimensions and mounting holes per CEA-310-E

Performance

Electrical

NEXT margin over TIA 568-C.2 component at 100MHz
Exceeds component requirements of TIA-568-C.2 Category 5e and ISO 11801 1-100MHz
Designed and tested for 1.5A of continuous current per pair

General Information

Manufacturing: 100% factory tested
Universal wiring (T568A or T568B)
Integrated labeling and icon slots for 606-B compliance


Mechanical

Mating Cycle: 2000+ with FCC 8-position plug

Applications

IEEE 802.3b 1000GBASE-T
IEEE 802.3bt PoE+
IEEE 802.3bt 4PPoE Power over Ethernet

HUBBELL



Accessories

Category 5e Component Jack	HXJ5EB
Category 5e Patch Cord	HC5EB03
Category 5E Panel Replacement Adaptor	HP5EM6
Category 5E UTP Cable	C5ESRB

Online Resources

Customer Use Drawing
eCatalog