Superstrut[®]

Pipe Straps, Conduit Clamps and Hangers

C-716 — Isolator for Copper Tubing

Features:


Designed for use with Superstrut® channel and pipe straps and Superstrut® C-711 Hangers. and may also be used with all standard flatbar or malleable iron hangers.

Materials:

Manufactured from one-piece steel shell with reinforcing ribs for stiffening and alignment. Padding is of processed non-conducting hairfelt and is cemented to the metal. Design of ribs creates a hinge so isolator may be opened and closed to install.

Application:

To provide a means to effectively isolate copper tubing from its supports to prevent the transmission of sound and vibration.



CAT. NO.	SIZE (IN.)	NOMINAL PIPE SIZE (IN.)	HANGER, C-711 OR PIPE STRAP, 702	WIDTH A (IN.)	STD. CTN.	
C716 1/2	1/2	1/2	3/4	21/8	100	
C-716-3/4	3/4	3/4	3/4	23/8	100	
C-716-1	1	1	1	23/8	100	
C-716-1-1/4	11/4	11/4	11/4	23/8	50	
C-716-1-1/2	11/2	1½	1½	23/8	50	
C-716-2	2	2	21/2	23/8	50	
C-716-2-1/2	21/2	21/2	3	215/32	50	
C-716-3	3	3	31/2	23/8	50	
C-716-3-1/2	31/2	3½	4	41/4	30	
C-716-4	4	4	5	41/4	20	

Order by Cat. No. and size. Standard Finish - GoldGalv®

S716 — Cushioned Strip — For Isolation and Vibration Applications


For use with 701 O.D. tubing and pipe clamp. To determine 701 clamp size, add 1/4" to 0.D. tube size to allow for the cushioned strip material.


1/4" markings for fast measuring and cutting. Measurement chart is printed on back of carton. 20 feet included in each carton.

Prevent metal-to-metal contact with the cushioned strip material. It aids in sound insulation, shock absorption and protects against corrosion, distortion and abrasion. Cushioned strip material is designed for optimal use between -30° F and 300° F. Cushioned strip material combined with the Superstrut® 701 pipe strap can handle clamping assignments from 1/4" to 6.



Sold in a carton of 20 feet.






Order 701 clamp separately.



C-708-U — Short Strap for Channel or Wall Mounting



CAT. NO.	P i PE S i ZE	Α	В	HOLE Size	STOCK S i ze	DESIGN Load LBS.	STD. CTN.
C-708-U-1/2	1/2	21/8	2	9/32	1/8 x 15/8	650	50
C-708-U-3/4	3/4	31/16	23/16	9/32	1/8 x 15/8	650	50
C-708-U-1	1	33//8	21/2	9/32	1/8 x 15/8	650	50
C-708-U-1-1/4	11/4	311/16	23/16	9/32	1/8 x 15/8	650	25
C-708-U-1-1/2	1½	315/16	31/16	9/32	1/8 x 15/8	650	25
C-708-U-2	2	5¾	41/8	7/ ₁₆	1⁄4 X 15⁄8	650	25
C-708-U-2-1/2	21/2	63/16	4%16	7/16	1⁄4 X 15∕8	1,000	25
C-708-U-3	3	6¾6	$5\frac{3}{16}$	7∕ ₁₆	1⁄4 X 15∕8	1,000	25
C-708-U-3-1/2	31/2	75/16	511/16	7/16	1/4 x 1 15/32	1,000	25
C-708-U-4	4	713/16	$6\frac{3}{16}$	7/16	1/4 x 1 15/32	1,200	25
C-708-U-5	5	87/8	71/4	⁷ / ₁₆	1/4 x 1 15/32	1,200	10
C-708-U-6	6	915/16	85/16	7/16	½ x 1%	1,200	10
Carbon Steel.							

Standard Finish - GoldGalv®

www.tnb.com

United States

Tel: 901.252.8000 800.816.7809 Fax: 901.252.1354

Technical Services Tel: 888.862.3289

Thomas & Betts