

# Dry Type Transformers General Purpose Encapsulated Single-Phase NEMA 3R

## Section 10

### 5 - 25 kVA Indoor/Outdoor Type QMS 115°C Rise UL Listed C-UL Listed

Input Voltage	Output Voltage	kVA	Frequency (Hz)	Taps	Wiring Diagram No. <sup>1</sup>	Weight (Lbs)	Frame Size	Product Number
120 x 240 Volts	120/240 Volts	5	60 Hz	No Taps	1	103	16350	9T21B1001G02
120 x 240 Volts	120/240 Volts	7.5	60 Hz	No Taps	1	147	16600	9T21B1002G02
120 x 240 Volts	120/240 Volts	10	60 Hz	No Taps	1	198	19400	9T21B1003G02
120 x 240 Volts	120/240 Volts	10	60 Hz	No Taps	1	198	19400	9T21B1054G02
120 x 240 Volts	120/240 Volts	15	60 Hz	No Taps	1	220	19500	9T21B9101
120 x 240 Volts	120/240 Volts	15	60 Hz	No Taps	1	233	19550	9T21B9131
120 x 240 Volts	120/240 Volts	25	60 Hz	No Taps	1	233	19550	9T21B9102
208 Volts	120/240 Volts	5	60 Hz	No Taps	4	103	16350	9T21B1028G02
208 Volts	120/240 Volts	7.5	60 Hz	No Taps	4	147	16600	9T21B1029G02
208 Volts	120/240 Volts	10	60 Hz	No Taps	4	198	19400	9T21B1030G02
208 Volts	120/240 Volts	15	60 Hz	No Taps	4	220	19500	9T21B9119
208 Volts	120/240 Volts	25	60 Hz	No Taps	4	388	50500	9T21B9120

<sup>1</sup>See page 10-45 for wiring diagrams.

<sup>2</sup>For Outdoor NEMA 3R Enclosure add suffix G62 to product number.

### 5 - 25 kVA Indoor/Outdoor Type QMS 115°C Rise UL Listed C-UL Listed

Input Voltage	Output Voltage	kVA	Frequency (Hz)	Taps	Wiring Diagram No. <sup>1</sup>	Weight (Lbs)	Frame Size	Product Number
277 Volts	120/240 Volts	5	60 Hz	(-2 5.1%)	2	103	16350	9T21B1046G02
277 Volts	120/240 Volts	5	60 Hz	(-2 2.5%)	2	103	16350	9T21B1265G02
277 Volts	120/240 Volts	7.5	60 Hz	(-2 5.1%)	2	147	16600	9T21B1047G02
277 Volts	120/240 Volts	10	60 Hz	(-2 5.1%)	2	198	19400	9T21B1048G02
277 Volts	120/240 Volts	10	60 Hz	(-2 2.5%)	2	198	19400	9T21B1266G02
277 Volts	120/240 Volts	15	60 Hz	(-2 5.1%)	2	220	19500	9T21B9143
277 Volts	120/240 Volts	25	60 Hz	(-2 4.7%)	2	388	50500	9T21B9144

<sup>1</sup>See page 10-45 for wiring diagrams.

### 5 - 25 kVA Indoor/Outdoor Type QMS 115°C Rise UL Listed C-UL Listed

Input Voltage	Output Voltage	kVA	Frequency (Hz)	Taps	Wiring Diagram No. <sup>1</sup>	Weight (Lbs)	Frame Size	Product Number
240 x 480 Volts	120/240 Volts	5	60	No Taps	1	103	16350	9T21B1004G02
240 x 480 Volts	120/240 Volts	5	50	No Taps	1	115	16400	9T21B1055G02
240 x 480 Volts	120/240 Volts	7.5	60	No Taps	1	147	16600	9T21B1005G02
240 x 480 Volts	120/240 Volts	7.5	50	No Taps	1	174	16600	9T21B1056G02
240 x 480 Volts	120/240 Volts	10	60	No Taps	1	198	19400	9T21B1006G02
240 x 480 Volts	120/240 Volts	10	50	No Taps	1	198	19400	9T21B1057G02
240 x 480 Volts	120/240 Volts	15	60	No Taps	1	220	19500	9T21B9103
240 x 480 Volts	120/240 Volts	15	50	No Taps	1	233	19550	9T21B9133
240 x 480 Volts	120/240 Volts	25	60	No Taps	1	388	50500	9T21B9104
240 x 480 Volts	120/240 Volts	25	50	No Taps	1	428	50600	9T21B9134
480 Volts	120/240 Volts	5	60	(-2 5.0%)	2	103	16350	9T21B1007G02
480 Volts	120/240 Volts	5	60	(+2,-2 2.5%)	3	103	16350	9T21B1013G02
480 Volts	120/240 Volts	7.5	60	(-2 5.0%)	2	147	16600	9T21B1008G02
480 Volts	120/240 Volts	7.5	60	(+2,-2 2.5%)	3	147	16600	9T21B1014G02
480 Volts	120/240 Volts	10	60	(-2 4.9%)	2	198	19400	9T21B1009G02
480 Volts	120/240 Volts	10	60	(+2,-2 2.6%)	3	198	19400	9T21B1015G02
480 Volts	120/240 Volts	15	60	(-2 5.0%)	2	220	19500	9T21B9105
480 Volts	120/240 Volts	15	60	(+2,-2 2.5%)	3	220	19500	9T21B9109
480 Volts	120/240 Volts	25	60	(-2 5.0%)	2	388	50500	9T21B9106
480 Volts	120/240 Volts	25	60	(+2,-2 2.5%)	3	388	50500	9T21B9110
600 Volts	120/240 Volts	5	60	No Taps	5	103	16350	9T21B1016G02
600 Volts	120/240 Volts	5	60	(-2 5.0%)	2	103	16350	9T21B1019G02
600 Volts	120/240 Volts	5	60	(+2,-2 2.5%)	107	16350	9T21B1025G02	
600 Volts	120/240 Volts	7.5	60	(-2 5.0%)	2	147	16600	9T21B1020G02
600 Volts	120/240 Volts	10	60	(-2 4.9%)	2	198	19400	9T21B1021G02
600 Volts	120/240 Volts	15	60	No Taps	5	220	19500	9T21B9111
600 Volts	120/240 Volts	15	60	(-2 4.8%)	2	220	19500	9T21B9113
600 Volts	120/240 Volts	25	60	(-2 5.0%)	2	388	50500	9T21B9114

<sup>1</sup>See page 10-45 for wiring diagrams.