

Project: \_\_\_\_\_ Type: \_\_\_\_\_

Drawn by: \_\_\_\_\_ Catalogue #: \_\_\_\_\_ Date: \_\_\_\_\_

## Individual Spec Sheet

# WTL

## LED ADJUSTABLE WALL PACK

Selectable color temperature (3 000/4 000/5 000 K)

Power selectable

Integrated photocell

Multi-Voltage (120-347 V)

### ORDERING INFORMATION

**Order code:** 68768  
**Model number:** WTL-PS30A-Q-3C-BR-P  
**UPC:** 069549019096  
**Case quantity:** 4

### PHYSICAL DATA

**Dimensions:** 7.31" x 6.49" x 4.54" (185.8 mm x 164.9 mm x 115.2 mm)  
**Lens material:** Clear polycarbonate lens  
**Housing material:** Die-Cast

### PERFORMANCE DATA

**Watts (W):** 15/30  
**Volts (VAC):** 120-347  
**Color temperature (K)<sup>1</sup>:** 3 000/4 000/5 000  
**Lumen output (lm)<sup>2</sup>:** 2 099- 4 090  
**Efficiency (lm/W):** 124-141  
**CRI:** 70  
**Photocell (Yes/No)** Yes  
**Dimming (Yes/No)** Yes  
**Power factor:** ≥0.9  
**THD (%):** ≤20  
**Frequency (Hz):** 50/60  
**Surge protection (kV):** 6  
**Operating temp. range:** -40 °C to +50 °C

<sup>1</sup> Typical colour temperature range: +/- 5 %

<sup>2</sup> Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %



ICES  
005




IK07



This lighting equipment complies with Canadian standard ICES-005 for use in commercial applications. Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.


**DIMENSIONS**



**PHOTOMETRIC DATA<sup>1</sup>**

**68768 • WTL-PS30A-Q-3C • 15 W • 4 000 K • 2 099 lm**

**Polar candela distribution**



**Zonal lumen summary**

Zone	Lumens	% Fixture
0-30	772.4	36.8%
0-40	1 233.5	58.8%
0-60	1 898.7	90.5%
60-90	181.0	8.6%
70-100	55.0	2.6%
90-120	5.0	0.2%
0-90	2 079.7	99.1%
90-180	18.9	0.9%
0-180	2 098.6	100%


**Illuminance at a distance**

Center beam fc		Beam width	
17'	3.40	29.1'	52.1'
34'	0.85	58.2'	104.3'
51'	0.38	87.3'	156.4'
68'	0.21	116.3'	208.5'
85'	0.14	145.4'	260.7'
102'	0.09	174.5'	312.8'

Vert. spread: 81.1°  
Horiz. spread: 113.8°

**68768 • WTL-PS30A-Q-3C • 30 W • 4 000 K • 4 089.5 lm**

**Polar candela distribution**



**Zonal lumen summary**

Zone	Lumens	% Fixture
0-30	1 396.1	34.1%
0-40	2 243.9	54.9%
0-60	3 630.7	88.8%
60-90	420.7	10.3%
70-100	122.3	3%
90-120	10.0	0.2%
0-90	4 051.3	99.1%
90-180	37.6	0.9%
0-180	4 089.0	100%

**Illuminance at a distance**

Center beam fc		Beam width	
17'	6.18	33.0'	49.6'
34'	1.54	65.9'	99.3'
51'	0.69	98.9'	148.5'
68'	0.39	131.9'	198.5'
85'	0.25	164.9'	248.2'
102'	0.17	197.8'	297.8'

Vert. spread: 88.2°  
Horiz. spread: 111.2°

<sup>1</sup> Complete IES files available on our website.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: \_\_\_\_\_  
 Company: \_\_\_\_\_  
 Signature: \_\_\_\_\_

Date: \_\_\_\_\_

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.