

Product data sheet

Characteristics

BR1000MS

APC Back-UPS Pro, 1000VA/600W, Tower, 120V, 10x NEMA 5-15R outlets, Sine Wave, AVR, USB Type A + C ports, LCD, User Replaceable Battery



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	600 W
Rated power in VA	1000 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA
Output connection type	6 NEMA 5-15R 4 NEMA 5-15R surge
Cable length	6 ft (1.8 m)
Number of cables	1
Battery Type	Lead-Acid battery

Batteries & Runtime

Included Battery Modules	1
Battery Slots Empty	0
Typical recharge time	16 h
RBC Quantity	1
Battery Voltage	24 V
Battery Capacity	7.0 Ah
Battery Charge Power (Watts)	8 W rated
Battery Life	3...5 year(s)
Extendable Run Time	0

General

Provided equipment	Coaxial cable User Manual USB cable
Product web sub-family	Gaming performance
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

Color	Black
Height	10.2 in (26 cm)
Width	3.9 in (10 cm)
Depth	14.5 in (36.8 cm)
Net Weight	22.5 lb(US) (10.2 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	No

Input

Input Frequency	60 Hz +/- 3 Hz
Efficiency at full load	88...147 V
Maximum Input Current per Phase	12 A
Switching current capacity	15 A

Output

Max Configurable Power (Watts)	600 W
Output Frequency (sync to mains)	60 Hz +/- 3 Hz sync to mains
Topology	Line Interactive
Waveform Type	Sine wave
Maximum configurable power in VA	1000 VA
Transfer Time	8ms typical : 10 ms maximum

Conformance

Product Certifications	ENERGY STAR V2.0 (USA)[RETURN]NOM[RETURN]TUV C-US certified
Equipment protection policy	Lifetime : \$250000

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...10000 ft (0.0000000000...3048.0000000000 m)
Acoustic level	45 dBA

Communications & Management

Control panel	Multi-function LCD status and control console
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge energy rating	1080 J
Filtering	Full time multi-pole noise filtering :5% of IEEE surge let-through : zero clamping response time: in

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	00731304335382
Returnability	No
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.12 in (35.87 cm)
Package 1 Width	19.0 in (48.2 cm)
Package 1 Length	8.8 in (22.3 cm)
Package 1 Weight	26.01 lb(US) (11.8 kg)
SCC14	10731304335389

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	"WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov "
ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------