



PL-T Triple 4-Pin Base

PL-T 26W/827/A/4P 1CT/5X10BOX ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum effciency and sleek design solutions are required.

Product data

General Information				
Cap-Base	GX24Q-3 [GX24q-3]			
LSF Preheat 2000 h Rated	99 %			
LSF Preheat 4000 h Rated	98 %			
LSF Preheat 6000 h Rated	97 %			
LSF Preheat 8000 h Rated	90 %			
Light Technical				
Color Code	827 [CCT of 2700K]			
Luminous Flux (Nom)	1750 lm			
Luminous Flux (Rated) (Nom)	1750 lm			
Color Designation	Incandescent White			
Correlated Color Temperature (Nom)	2700 K			
Luminous Efficacy (rated) (Nom)	64.8 lm/W			
Color Rendering Index (Nom)	82			
LLMF 2000 h Rated	92 %			
LLMF 4000 h Rated	88 %			
LLMF 6000 h Rated	85 %			
LLMF 8000 h Rated	84 %			

81 %
27.0 W
0.335 A
28 ℃
Yes
4P
1.4 mg


Datasheet, 2021, July 30 data subject to change

PL-T Triple 4-Pin Base

Product Data	
Order product name PL-T 26W/827/A/4P 1CT/5X10BOX AI	
EAN/UPC - Product	046677384401
Order code	458240
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10


Material Nr. (12NC)	927910982750		
Net Weight (Piece)	64.000 g		
ILCOS Code	FSM-26/27/1B-E-GX24q=3		


Dimensional drawing



Product	D (max)	A (max)	B (max)	C (max)
PL-T 26W/827/A/4P/ALTO	41 mm	86.7 mm	111.0 mm	126.7 mm

Photometric data







Lightcolor /827

Lightcolor /827

Lifetime






Lumen Maintenance 3 h and 12 h cycle

Life Expectancy 3 h cycle

PL-T Triple 4-Pin Base

Lifetime



Life Expectancy 12 h cycle

