Ignitor Specifications (Case Temperature Rating 105°C)

Metal Halide

HID



				Me	tal Halide							
Ballast Data				Standard Ignitor			Long Range Ignitor					
Philips Advance Ballast Family	Lamp Watts	ANSI Code	Ballast Circuit Type	Catalog Number	Max. Dist. (ft.) To Lamp	Case Type		Catalog Number	Min. Dist. (ft) To Lamp	Max. Dist. (ft) To Lamp	Case Type	
71A5105	50	MI10/148	HX	LI533-H4-IC	15	Round	1	XTENZA® Lo	ng-Range I	gnitor		
71A51_1	50	MI10/148	HX	LI533-H4-IC	10	Round		- Meets ANSI pul			t to lamp	
71A5137	50	MI10/148	R	LI533-H4-IC	2	Round		distances from (
71A5205	70	M98/143	HX	LI533-H4-IC	25	Round		- Features 105°C		ture rating		
71A52_2	70	M98/143	HX	LI533-H4-IC	15	Round		- See Ordering In				
71A5237	70	M98/143	R	LI533-H4-IC	10	Round	(
71A52_1	70	MI 39	HX	LI533-H4-IC	10	Round		LI533-LR1	0 -	50 ft	Oval	
71A53_0	100	M90/140	HX	LI533-H4-IC	20	Round						
71A5383	100	M90/140	CWA	LI533-H4-IC	2	Round						
71A5337	100	M90/140	R	LI533-H4-IC	2	Round	J					
71A54 2	150	MI02/142	HX	LI533-H4-IC	10	Round	1	~				
71A5437	150	MI02/142	R	LI533-H4-IC	2	Round			-36	A Present		
71A55-3	175	MI37/152	SuperCWA	LI533-H4-IC	2	Oval				e Renvi	12	
71A56 2	200	M136	SuperCWA	LI533-H4-IC	2	Round				and the		
71A56 3	200	M136	SuperCWA	LI533-H4-IC	5	Round						
71A572	250	MI38/153		LI533-H4-IC	5	Round	i s	•				
71A58 2	320	MI32/154	SuperCWA	LI533-H4-IC	2	Round		LI533-LR	0 -	50 ft	Oval	
71A59 3	350	MI3I	SuperCWA	LI533-H4-IC	2	Round						
71A60 2	400	MI35/155	SuperCWA	LI533-H4-IC	10	Round						
71A61E6	400	MI35/155	SuperCWI	LI533-H4-IC	2	Round						
71A63_3	450	MI44	Super CWA	LI533-H4-IC	5	Round	1					
71A64 0	750	M149	SuperCWA	LI573-H5	15	Oval	1					
71A64_2	750	MI49	SuperCWA	LI573-H5-IC	15	Oval						
71A64 8	875	M-166	SuperCWA	LI572-H5-IC*	10	Oval	1	LI533-LR3*	0 -	50 ft	Oval	
71A65_1	1000	MI41	SuperCWA	LI572-H5-IC*	10	Oval			1 -			
71A65 3	1000	MI41	SuperCWA	LI571-H5-IC*	5	Oval	1					
71A50 5	35	M130	HX	LI533-H4-IC	15	Round	-	LI561-H5 *	15	50	Oval	
71A5081	35	MI30	HX	LI533-H4-IC	15	Round		LI561-H5★	15	50	Oval	
71A5037	35	M130	R	LI533-H4-IC	10	Round		LI561-H5*	10	50	Oval	
71A52 0	70	M85	HX	LI522-H5-IC*	30	Oval		2.001110	Not Availa			
71A54A3	150	MI02/142		LI501-I4-IC*	15	Round		Not Available				
71A54 0	150	M81	HX	LI522-H5-IC*	20	Oval			Not Availa			
71A5486	150	M81	CWA	LI523-H5-IC*	2	Oval		Not Available				
71A5880	250	M80	HX	LI522-H5-IC*	5	Oval			Not Availa			
71A86 5	750	**	CWA	LI561-H5-IC*	5	Oval			Not Availa			


 \star Equipped with an auto-rest thermal protector to help prevent ignitor from overheating in the event of lamp failure


XTENZA Ordering Information

To order in bulk, specify item no. LI533-LR, LI533-LR1 or LI533-LR3. For individual carton, add -IC to item no.

XTENZA is also available packaged with the ballasts shown at right.







MI 30 35 35 MI 30 70 M98/14 70 M98/14 70 M98/14 100 M90/140 71A5383 100 M90/140 71A5390

Lamp

Watts

ANSI	Ballast	No	With Welded
Code	Number	Bracket	Bracket
MI 30	71A5005		-910DP
MI 30	71A5081	-900D	
198/143	71A5205		-910DP
198/143	71A5292	-900D	
198/143	71A52A2	-900D	-910D
190/140	71A5383		-910D

-900D

Oval Case

RW33CC1252

all -IC suffix replacement ignitors.

MOUNTING CLIP for Round Case

(Furnished as standard with -001 suffix ballasts and

5-41




LISOD


The Philips Advance shut-off device (LISOD[™]) enhances the reliability of High Intensity Discharge (HID) lighting systems where ignitors are utilized to start the HID lamps. This includes all high pressure sodium lamps as well as all low, medium, and high wattage pulse-start metal halide lamps. The LISOD shut-off device is used in addition to a standard ignitor.

The LISOD shut-off device increases the life of the ignitor by disabling it from the circuit and eliminating any concern over long-term ballast reliability due to continuously pulsing ignitors when a lamp is burned out. The LISOD provides a simple solution to eliminate lamp cycling typically associated with lamps that have reached their end of life. The LISOD disables the ignitor after 15 minutes of pulsing in cases when lamp is taken out of socket or lamp fails to ignite.

- Compatible with any Philips Advance Reactor (R), High-Reactance (HX), and Constant Wattage Autotransformer (CWA) ballast and ignitor circuit that includes a 120V input tap.
- Integral timer automatically disables ignitor from ballast circuit I5-minutes after power is applied to the ballast
- Extends ignitor life, which is typically rated for 10,000 hours of continuous pulsing
- Protects ballast coil insulation from potential damage due to a continuously pulsing ignitor
- Prevents cycling of end-of-life lamps making identification for lamp replacement easy
- Automatically resets/restarts itself after 0.6 second of power interruption (voltage dropout)

Catalog Number	Uescription			
LISOD 1 -IC	Ignitor shut-off device for HID CWA, HX, and R ballasts with ignitors. Individual carton packaging	L		
LISOD 1	Ignitor shut-off device for HID CWA, HX and R ballasts with ignitors. Bulk packaging	50		






Ignitor Specifications (Case Temperature Rating 105°C)




HID

				High Pressure S	Sodium				
	Ballast I	Data		Stand	ard Ignitor		Long Range Ignitor		
Phililps Advance Ballast Family	Lamp Watts	ANSI Code	Ballast Circuit Type	Catalog Number	Max. Dist. (ft.) To Lamp	Case Type	Catalog Number	Max. Dist. (ft.) To Lamp	Case Type
71A7707	35	S76	R	LI55 I -H4-IC	2	Round	LI55 I -J4-IC	15	Round
71A7801	50	S68	HX	LI55 I -H4-IC	2	Round	LI55 I -J4-IC	35	Round
71A7807	50	S68	R	LI55 I -H4-IC	2	Round	LI55 I -J4-IC	15	Round
71A79_1	70	S62	HX	LI55 I -H4-IC	2	Round	LI55 I -J4-IC	35	Round
71A79_6	70	S62	CWI	LI55 I -J4-IC	2	Round	Not Available		
71A79_8	70	S62	CWA	LI55 I -J4-IC	5	Round	Not	Available	
71A7907	70	S62	R	LI55 I -H4-IC	2	Round	LI55 I -J4-IC	15	Round
71A80_1	100	S54	HX	LI55 I -H4-IC	2	Round	LI55 I -J4-IC	35	Round
71A80_8	100	S54	CWA	LI55 I -J4-IC	5	Round	Not Available		
71A8007	100	S54	R	LI55 I -H4-IC	2	Round	LI55 I -J4-IC	15	Round
71A80_6	100	S54	CWI	LI55 I -J4-IC	2	Round	Not	Available	
71A81_2	150	S55	HX	LI55 I -H4-IC	2	Round	LI55 I -J4-IC	35	Round
71A81_8	150	S55	CWA	LI55 I -J4-IC	10	Round	Not Available		
71A8107	150	S55	R	LI55 I -H4-IC	2	Round	LI55 I -J4-IC	15	Round
71A8156	150	S55	CWI	LI55 I -J4-IC	2	Round	Not Available		
71A85_5	150	S55	CWI	LI55 -J4-IC	2	Round	Not Available		
71A81_6	150	S56	CWA	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round
71A86_7	150	S56	R	LI501-H4-IC	2	Round	LI50 I -J4-IC	50	Round



Round Case



Oval Case



RW33CC1252 Mounting Clip for Round Case (Furnished as standard with -001 suffix ballasts and all -IC suffix replacement ignitors.





B


Ignitor Specifications (Case Temperature Rating 105°C)

High Pressure Sodium


High Pressure Sodium										
Ballast Data				Stand	ard Ignitor		Long Range Ignitor			
Phililps Advance Ballast Family	Lamp Watts	ANSI Code	Ballast Circuit Type	Catalog Number	Max. Dist. (ft.) To Lamp	Case Type	Catalog Number	Max. Dist. (ft.) To Lamp	Case Type	
71A89_0	200	S66	CWA	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round	
71A89_1	200	S66	CWA	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round	
71A89_7	200	S66	R	LI501-H4-IC	2	Round	LI50 I -J4-IC	50	Round	
71A82_1	250	S50	CWA	LI501-H4-IC	2	Round	LI50 I -J4-IC	50	Round	
71A82_6	250	S50	CWI	LI501-J4-IC	2	Round	Not Available			
71A82_7	250	S50	R	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round	
71A8392	250	S50	CWA	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round	
71A83_1	310	S67	CWA	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round	
71A83_7	310	S67	R	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round	
71A84_3	400	S5 I	CWA	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round	
71A84_6	400	S5 I	CWI	LI501-J4-IC	2	Round	Not Available			
71A84_7	400	S5 I	R	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round	
71A85_6	430	n/a	CWI	LI501-H4-IC	15	Round	LI501-J4-IC	35	Round	
71A85_5	600	S106	CWA	LI561-H5-IC	5	Oval	Not Available			
71A85_8	600	S106	CWI	LI561-H5-IC	2	Oval	Not Available			
71A86_5	750	SIII	CWA	LI561-H5-IC	5	Oval	Not Available			
71A87_3	1000	S52	CWA	LI571-H5-IC★	15	Oval	LI57 I -J5-IC★	75	Oval	

HID • Ignitors HPS

 \bigstar Equipped with an auto-rest thermal protector to help prevent ignitor from overheating in the event of lamp failure.



Round Case



Oval Case



RW33CC1252 Mounting Clip for Round Case (Furnished as standard with -001 suffix ballasts and all -IC suffix replacement ignitors.