



SKU: SK-2

UPC: 0783669819069

Features & Benefits:

Description: Copper Split Bolt, Dual Rated, Conductor Range for Equal Main & Tap 2-8 Sol, Tin Plated, UL, CSA

Specs

Additional Class Attributes

Connection	Mechanical
Number of Conductors	1
Number of Poles	1

Conductor Ranges

Conductor Range AL Solid (Secondary, tap, load)	8 Sol
Conductor Range AL Stranded (Primary, run, main, line)	2 Str - 8 Str
Conductor Range AL Stranded (Secondary, tap, load)	2 Str - 8 Str
Conductor Range CU Solid (Primary, run, main, line)	8 Sol
Conductor Range CU Solid (Secondary, tap, load)	8 Sol
Conductor Range CU Stranded (Primary, run, main, line)	2 Str - 8 Str
Conductor Range CU Stranded (Secondary, tap, load)	2 Str - 8 Str
Conductor Range for Equal Run & Tap ACSR	2 ACSR - 6 ACSR
Conductor Range for Equal Run & Tap Str	2 Str - 6 Str
Conductor Range for Equal Run & Tap Sol	2 Sol - 8 Sol
Conductor Range for Minimum Tap with Maximum Run	8 Sol
Conductor Range AL Solid (Primary, run, main, line)	8 Sol
Max Conductor Copperweld - Str	3 No. 7
Max Conductor Copperweld - Type A	3A

Dimensions

Drive Size Main	13/16
Drive Type Main	External Hex
Height (IN)	0.81
Height BX (IN)	2
Length (IN)	1.55
Weight (LB)	0.13
Weight BX (LB)	7.7981
Width (IN)	0.93
Width BX (IN)	6.1875
Wire Diameter Range Primary (IN)	0.128 - .316

Material and Finish

Conductor Material	Copper
Connector Finish	Tin

Insulation	NA
Material	Copper
Wire Binding Hardware Finish	Tin
Wire Binding Hardware Material	Copper

Additional Technical Specifications

Conductor Type	Solid
----------------	-------

Bolt and Screw Sizes

Number of Wire Binding Screws per Port	1
Wire Binding Screw Size	NA
Wire Binding Torque	275

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 50
Direct Burial	No
Dual Rated	Yes
NEMA Code	S-588-4
UPC Code	78366981906

Testing Standards

CSA File Number	LR-701570
CSA Standard	C22.2 No. 65
Prop65 Compliance	WARNING: Cancer and Reproductive Harm - www.P65warnings.ca.gov
RUS Listed	Yes
UL Control Number	460C
UL / CULUS Specification	UL 486A/B Listed
UL File Number	E6207

Environment and Temperature

Temperature Rating	90°C
--------------------	------

Color

Color	Silver
-------	--------

Voltage

Voltage Rating	35 kV
----------------	-------