



**SKU:** SK-2/0

**UPC:** 0783669819106

**Features & Benefits:**

**Description:** Copper Split Bolt, Conductor Range for Equal Main & Tap 2/0-6, Tin Plated, UL, CSA

## Specs

### Additional Class Attributes

Connection	Mechanical
Number of Conductors	1
Number of Poles	1

### Conductor Ranges

Conductor Range AL Solid (Secondary, tap, load)	NA
Conductor Range AL Stranded (Primary, run, main, line)	NA
Conductor Range AL Stranded (Secondary, tap, load)	NA
Conductor Range CU Solid (Primary, run, main, line)	NA
Conductor Range CU Solid (Secondary, tap, load)	NA
Conductor Range CU Stranded (Primary, run, main, line)	2/0 Str - 6 Str
Conductor Range CU Stranded (Secondary, tap, load)	2/0 Str - 6 Str
Conductor Range for Equal Run & Tap ACSR	1/0 ACSR - 6 ACSR
Conductor Range for Equal Run & Tap Str	2/0 Str - 6 Str
Conductor Range for Equal Run & Tap Sol	2/0 Sol - 5 Sol
Conductor Range for Minimum Tap with Maximum Run	10 Sol
Conductor Range AL Solid (Primary, run, main, line)	NA
Max Conductor Copperweld - Str	3 No. 5

### Dimensions

Drive Size Main	13/16
Drive Type Main	External Hex
Height (IN)	1
Height BX (IN)	2
Length (IN)	1.82
Weight (LB)	0.217
Weight BX (LB)	6.547
Width (IN)	1.15
Width BX (IN)	6.1875
Wire Diameter Range Primary (IN)	0.184 - 0.419

### Material and Finish

Conductor Material	Copper
Connector Finish	Tin
Insulation	NA

Material	Copper
Wire Binding Hardware Finish	Tin
Wire Binding Hardware Material	Copper

### Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

### Bolt and Screw Sizes

Number of Wire Binding Screws per Port	1
Wire Binding Screw Size	NA
Wire Binding Torque	385

### General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 20
Direct Burial	No
Dual Rated	No
NEMA Code	S-588-4
UPC Code	78366981910

### Testing Standards

CSA File Number	LR-701570
CSA Standard	C22.2 No. 65
Prop65 Compliance	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65warnings.ca.gov">www.P65warnings.ca.gov</a>
RUS Listed	Yes
UL Control Number	460C
UL / CULUS Specification	UL 486A/B Listed
UL File Number	E6207

### Environment and Temperature

Temperature Rating	90°C
--------------------	------

### Color

Color	Silver
-------	--------

### Voltage

Voltage Rating	35 kV
----------------	-------