



SKU: TA-6-S

UPC: 0783669888386

Features & Benefits:

Description: Aluminum Mechanical Lug, Conductor Range 4-14, 1 Port, 1 Hole, 1/4in Bolt Size, Tin Plated, UL, CSA

Specs

Additional Class Attributes

Connection	Mechanical
Contains DE-OX®	No
Mounting Hole Type	Thru
Number of Conductors	1
Number of Mounting Holes	1
Number of Poles	1
Number of Ports / Wireways	1

Dimensions

Dimension G (IN)	0.25
Dimension G (mm)	6.35
Drive Size Main	NA
Drive Type Main	Slotted
Height (IN)	0.5
Height BX (IN)	2.25
Length (IN)	1.062
Mounting Hole Diameter (IN)	0.265
Mounting Hole Diameter (mm)	6.731
Mounting Hole Spacing (mm)	0
Tang Length (IN)	0.687
Tang Length (mm)	17.4498
Tang Thickness (IN)	0.093
Tang Thickness (mm)	2.3622
Tang Width (IN)	0.5
Tang Width (mm)	12.7
Weight (LB)	0.043
Weight BX (LB)	2.7
Width (IN)	0.5
Width BX (IN)	5

Material and Finish

Conductor Material	Copper
Connector Finish	Tin
Insulation	NA
Material	Aluminum
Wire Binding Hardware Finish	Zinc Clear Trivalent Chromate
Wire Binding Hardware Material	Steel

Additional Technical Specifications

Conductor Type	Solid
----------------	-------

Bolt and Screw Sizes

Mounting Bolt/Stud Size	1/4
Number of Wire Binding Screws per Port	1
Wire Binding Screw Size	5/16
Wire Binding Torque	8 AWG = 40

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 100
Direct Burial	No
Dual Rated	Yes
NEMA Code	S-588-3
UPC Code	78366988838

Testing Standards

CSA File Number	LR-29601
CSA Standard	C22.2 No. 65-03
Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
ROHS Indicator	IND
UL Control Number	453G
UL / CULUS Specification	UL 486A/B Listed
UL File Number	E6207

Environment and Temperature

Temperature Rating	90°C
--------------------	------

Color

Color	Silver
-------	--------

Conductor Ranges

Conductor Range AL Solid (Secondary, tap, load)	NA
Conductor Range AL Stranded (Primary, run, main, line)	4 Str - 14 Str
Conductor Range AL Stranded (Secondary, tap, load)	NA
Conductor Range CU Solid (Primary, run, main, line)	10 Sol - 14 Sol
Conductor Range CU Solid (Secondary, tap, load)	NA
Conductor Range CU Stranded (Primary, run, main, line)	4 Str - 14 Str
Conductor Range CU Stranded (Secondary, tap, load)	NA
Conductor Range AL Solid (Primary, run, main, line)	10 Sol - 14 Sol
Wire Combinations	NA

Voltage

Voltage Rating

35 kV