

SKU: CLNS-4-14

UPC: 0783669630305

Features & Benefits:

Description: Surecrimp Copper Compression Lug, Conductor Size 4, 1 Hole, 1/4in Bolt Size, Long Barrel, No Sight Window, Tin Plated, UL, CSA



Specs

Additional Class Attributes

Barrel Marking	Ink
Barrel Type	Long
Connecting Angle	180°
Connection	Compression
Contains DE-OX®	Yes
Flared End	No
ILSCOs Die Catalog Number	ILD-29
ILSCOs Die Index Number	I-29
Mounting Hole Type	Thru
Narrow Tang	No
Number of Mounting Holes	1
Sight Window	No
Slotted	No
Tang End Shape	Square
Undrilled	No

Dimensions

Barrel Length (IN)	1.125
Barrel Length (mm)	28.575
Dimension G (IN)	0.321
Dimension G (mm)	8.1534
Height (IN)	0.373
Height BX (IN)	2.25
Height (mm)	9.4742
Inside Diameter (IN)	0.25
Inside Diameter (mm)	6.35
Length (IN)	2.039
Length (mm)	51.7906
Mounting Hole Diameter (IN)	0.281
Mounting Hole Diameter (mm)	7.1374
Mounting Hole Spacing (mm)	0
Outside Diameter (IN)	0.343
Outside Diameter (mm)	8.7122
Strip Length (mm)	30.1498
Tang Length (IN)	0.68
Tang Length (mm)	17.272
Tang Thickness (IN)	0.093
Tang Thickness (mm)	2.3622
Tang Width (IN)	0.486

Tang Width (mm)	12.3444
Weight (LB)	0.0262320444275115
Weight BX (LB)	2.23
Width (IN)	0.486
Width BX (IN)	5
Width (mm)	12.3444

Conductor Ranges

Conductor Range AL Stranded (Primary, run, main, line)	NA
Conductor Range CU Solid (Primary, run, main, line)	4 Sol
Conductor Range CU Stranded (Primary, run, main, line)	4 Str
Conductor Range AL Solid (Primary, run, main, line)	NA
Expanded Conductor Range	4 Str - 6 Str
Flex Conductor Range	NA

Material and Finish

Conductor Material	Copper
Connector Finish	Tin
Insulation	NA
Material	Copper

Additional Technical Specifications

Conductor Type	Solid
----------------	-------

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 50
Direct Burial	Yes
Dual Rated	No
NEMA Code	S-588-3
UPC Code	78366963030

Bolt and Screw Sizes

Mounting Bolt/Stud Size	1/4
-------------------------	-----

Testing Standards

CSA File Number	LR-29601
CSA Standard	C22.2 No. 65-03
NEBS Rating	Level 3
Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
UL Control Number	453G
UL / CULUS Specification	UL 467 Listed
UL File Number	E6207

Environment and Temperature

Temperature Rating	90°C
--------------------	------

Color

Color	Silver
Color Code	Gray

Voltage

Voltage Rating	35 kV
-----------------------	-------