



**SKU:** NBAS-010-1-B

**UPC:** 0783669005592

**Features & Benefits:**

**Description:** Aluminum Neutral Bar, Dual Rated, Conductor Range 4-14, 10 Ports, 1 Hole, #10 Bolt, Headless Slot Drive, UL, CSA

## Specs

### Additional Class Attributes

Connection	Mechanical
Mounting Hole Type	Thru
Number of Conductors	10
Number of Mounting Holes	1
Number of Poles	1
Number of Ports / Wireways	13
Number of Usable Ports	10
Type of Accessory	NBST-2/0

### Dimensions

Dimension G (IN)	2.052
Dimension G (mm)	52.1208
Drive Size Main	NA
Drive Type Main	Slotted
Height (IN)	0.437
Height BX (IN)	1.9
Height (mm)	11.0998
Length (IN)	4.104
Mounting Bolt/Stud Size (mm)	254
Mounting Hole Diameter (IN)	0.203
Mounting Hole Position (IN)	7
Weight (LB)	0.06
Weight BX (LB)	1.295
Width (IN)	0.312
Width BX (IN)	4

### Material and Finish

Conductor Material	Copper
Connector Finish	Tin
Insulation	NA
Material	Aluminum
Wire Binding Hardware Finish	Gold Zinc Chromate
Wire Binding Hardware Material	Steel

### Additional Technical Specifications

Conductor Type

Solid

### Bolt and Screw Sizes

Mounting Bolt/Stud Size	#10
Number of Wire Binding Screws per Port	1
Wire Binding Screw Size	1/4
Wire Binding Torque	4 - 6 AWG = 35

### General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 20
Dual Rated	Yes
NEMA Code	S-588-3
UPC Code	78366900559

### Testing Standards

CSA File Number	LR-29601
CSA Standard	C22.2 No. 65-03
Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
UL Control Number	NA
UL / CULUS Specification	UL 486A/B Recognized
UL File Number	E6207

### Color

Color

Silver

### Conductor Ranges

Conductor Range AL Solid (Secondary, tap, load)	NA
Conductor Range AL Stranded (Primary, run, main, line)	4 Str - 14 Str
Conductor Range AL Stranded (Secondary, tap, load)	NA
Conductor Range CU Solid (Primary, run, main, line)	10 Sol - 14 Sol
Conductor Range CU Solid (Secondary, tap, load)	NA
Conductor Range CU Stranded (Primary, run, main, line)	4 Str - 14 Str
Conductor Range CU Stranded (Secondary, tap, load)	NA
Conductor Range AL Solid (Primary, run, main, line)	10 Sol - 14 Sol

### Voltage

Voltage Rating

35 kV