

TECHNICAL DATA SHEET

ABB cable glands – STEX Star Teck® extreme series

Hazardous locations



The STAR TECK® STEX Explosion Proof fitting for Teck, MC and ACWU - its innovative design provides quality engineering, easier installation and helps achieve safer, more reliable terminations in challenging industrial environments. The STEX offers a broader cable range per fitting compared to the regular STX series.

Certifications / Standards:



IMPORTANT:

Must be installed with the SC4-KIT-1 sealing compound or the SC65 putty sealing compound. Sold separately. See sealing compounds information.

Features & Benefits:

- Excellent solution for hazardous location
- Excellent pullout strength
- Robust metallic construction
- Quick and easy installation without disasembly
- Extended clamping range taking
- Provides grounding continuity of cable armor
- Removable armor-stop for greater cable ranges

Applications:

- Provides means for passing jacketed metal clad cables through a bulkhead or enclosure in industrial and hazardous areas
- Construction and installation zones where metal clad cables are specified
- Suitable for Class 1 Div 1 areas
- Suitable for cable types:
 - Jacketed Teck
 - Armored control and instrument (ACIC Div2 locations)
 - Type MC: Jacketed corrugated metal clad (aluminum and steel)

Material:

- Copper free aluminum

Sealing compounds information:

- Use SC4-KIT-1 liquid compound for shielded cables and cables with 5 conductors or more (including ground).
- The SC65 is not recommended for use with shielded cables. Suitable for use on cables with a maximum of 4 conductors (including ground).
- Approximate Sealing Compound Volumes:
 SC4-KIT-1 = 50cc / SC65 = 34cc

Environmental ratings: Working Temperature:

- Normal use -40 to +90°C (-40 to +194°F)
- Ingress protection:
- Type 4 / 4X

Conforms to:

- CSA 22.2-25/ -30/ -174/ -94
- Class I Div1 ABCD Class II Div1 EFG Class III Div1
 UL2225
- Class I Div1 ABCD Class II Div1 EFG Class III Div1
- UL514B and CSA C22.2-18.3
- Wet and Dry Locations
- RoHS (Restriction of Hazardous Substances Directive) 2011/65/EU Incorporating 2015/863 amendment to Annex II

Part no:	Thread (NPT)	Max. Vol. of sealing compound	Range over jacket		Range over armour				Nominal dimensions		
			Min	Max	Min	Max	А	в	с	D1	D2
STEX075	3/4	8	15.24	25.02	13.21	22.73	20.07	86.36	46.23	12.70	17.02
			(0.600)	(0.985)	(0.520)	(0.895)	(0.790)	(3.400)	(1.820)	(0.500)	(0.670
STEX100	1	16	21.84	30.61	19.81	28.58	25.02	90.93	61.98	16.38	20.96
			(0.860)	(1.205)	(0.780)	(1.125)	(0.985)	(3.580)	(2.440)	(0.645)	(0.825
STEX125	1-1/4	23	24.13	34.93	22.10	32.89	25.65	99.57	64.01	21.06	27.3
			(0.950)	(1.375)	(0.870)	(1.295)	(1.010)	(3.920)	(2.520)	(0.829)	(1.076
STEX150	1-1/2	43	29.21	41.28	25.15	37.21	26.16	127.51	83.31	24.21	32.5
			(1.150)	(1.625)	(0.990)	(1.465)	(1.030)	(5.020)	(3.280)	(0.953)	(1.280
STEX200	2	72	36.58	49.91	32.51	45.85	26.92	130.05	92.46	31.62	39.7
			(1.440)	(1.965)	(1.280)	(1.805)	(1.060)	(5.120)	(3.640)	(1.245)	(1.565
STEX250	2-1/2	147	46.36	60.33	42.29	56.26	40.13	131.32	115.32	41.40	50.8
			(1.825)	(2.375)	(1.665)	(2.215)	(1.580)	(5.170)	(4.540)	(1.630)	(2.000
STEX300	3	286	57.53	72.14	53.47	68.07	41.66	167.89	125.22	52.48	63.3
			(2.265)	(2.840)	(2.105)	(2.680)	(1.640)	(6.610)	(4.930)	(2.066)	(2.495
STEX350	3-1/2	366	67.82	83.06	64.64	79.88	42.93	187.45	147.07	64.06	73.5
			(2.670)	(3.270)	(2.545)	(3.145)	(1.690)	(7.380)	(5.790)	(2.522)	(2.895
STEX400	4	614	81.79	98.30	78.49	92.46	44.20	194.31	157.23	77.72	89.4
			(3.220)	(3.870)	(3.090)	(3.640)	(1.740)	(7.650)	(6.190)	(3.060)	(3.520

Bold numbers are metric, parenthesis numbers are inches.

Note: Product must be installed in accordance with applicable national and local electrical codes.

REMOVABLE ARMOR STOP, SEE "D" DIMENSIONS D1 = WITH ARMOR STOP D2 = WITHOUT ARMOR STOP

D1 -D2→

THREAD

CLI ABCD,

А

tnb.abb.com (US/Latin America) tnb.ca.abb.com (Canada) abb.com We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction – in whole or in part – is forbidden without prior written consent of ABB. Copyright© 2019 ABB. All rights reserved.

