

Project: \_\_\_\_\_ Type: \_\_\_\_\_

Drawn by: \_\_\_\_\_ Catalogue #: \_\_\_\_\_ Date: \_\_\_\_\_

## Individual Spec Sheet

# SWIVEL CHOICE LED DOWNLIGHT

### ORDERING INFORMATION

**Order code:** 68672  
**Model number:** SWDL4R-8A-3CBK/CHOICE  
**UPC:** 069549018334  
**Case quantity:** 32

### PHYSICAL DATA

**Size in. (cm):** 4 (10.6)  
**Shape:** Round  
**Finish:** Black  
**Lens type:** Frosted polycarbonate



### PERFORMANCE DATA

**Watts (W):** 8  
**Volts (VAC):** 120  
**Colour temp. (K):** 2 700/3 000/4 000  
**Lumen output (lm):** 600  
**Lumen per Watts (lm/W):** 75  
**CRI:** 90+  
**Life L70 (h):** 50 000  
**Beam angle (°):** 45  
**Environment:** Wet location  
**THD (%):** <15  
**Power factor:** >0.9  
**Frequency (Hz):** 60  
**Operating temp. range:** - 30 °C / - 22 °F to 40 °C / 104 °F  
**Cable rating:** FT4  
**Dimmable:** Yes

<sup>1</sup> Typical colour temperature range: +/- 5 %  
<sup>2</sup> Lumens values from Energy Star reported data.  
<sup>3</sup> Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations

### COMPATIBLE ACCESSORIES

Order code	Model number	Type
66050	ACC/MPLATE/3.75IN/SQR/STD	Square mounting plate
66057	ACC/MPLATE/3.75IN/ADJ/STD	Adjustable mounting plate




This lighting equipment complies with Canadian standard ICES-005 for use in residential applications. Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

**COMPATIBLE DIMMERS**

Brand	Model
LEGRAND	RH703PTUTC
COOPER	AAL06, SLC03P
LEVITON	IPL06, 6674, DSL06-1ZL, DSM10-1LZ, IPE04-1LZ, DDMX1
LUTRON	PD-5NE, RRD-6NA, PD-6WCL, DVCL-153P, CTCL-153P, DVCL-253P, AYCL-253P, DVRP-253, SELV-300P, MACL-153P

NOTE: The above table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation. Some dimmers may require more than one product for stable operation. The maximum number of products is determined by the dimmer wattage rating with LEDs. Be careful, these dimmers have different ratings depending on the product type. Again, refer to the dimmer installation instructions.


**DIMENSIONS**



**PHOTOMETRIC DATA<sup>1</sup>**

**68672 • SWDL4R-8A-3CBK/CHOICE-30K • 642.8 lm**

**Polar candela distribution**



**Zonal lumen summary**

Zone	Lumens	% Fixture
0-30	435.6	67.8
0-40	537.5	83.6
0-60	621.0	96.6
60-90	21.8	3.4
0-90	642.8	100

**Illuminance at a distance**

	Center beam fc	Beam width
2.0'	246.9	1.5'
4.0'	61.7	3.0'
6.0'	27.4	4.5'
8.0'	15.4	6.0'
10.0'	9.9	7.4'

■ Vert. spread: 40.8°

<sup>1</sup> Complete IES files available on our website.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: \_\_\_\_\_  
 Company: \_\_\_\_\_  
 Signature: \_\_\_\_\_

Date: \_\_\_\_\_

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.