

Non Metallic Conduit Grey

Applications

- Fiber optics
- Automatic & moving machinery
- Robotics
- Lasers
- Office equipment
- Marine/shipboard wiring
- Extreme flexibility
- Broad temperature range-remains flexible from -5° to 176°F
- Liquid-tight
- One piece construction



UL File No. LL-84705
CSA File No. E129973



C(UL) E19675

Non-Metallic Conduit - GRAY
Code
NMC –
Available in sizes from 6 mm to 53 mm (1/4" to 2") Please contact office for more details.

Non-Metallic Connectors— Straight—Gray	Non-Metallic Connectors— 90 Degree-Gray
Code	Code
C-NMQL –	C-NMQL – 90
Available in sizes from 6 mm to 53 mm (1/4" to 2"). Please contact office for more details	

C (UL) US File No. E19675

Non Metallic Ultra Flexible Black

Applications

- Direct earth burial applications
- Chemical processing
- HVAC equipment
- Computer power installations
- Water treatment systems
- Marine equipment
- Crush, abrasion and strain-resistant
- Sunlight resistant
- Liquid-tight
- Broad temperature range from -5° to 176°F
- Smooth interior finish



UL File No. LL-84707
CSA File No. E122972



C(UL) E19675

Non-Metallic Ultra Conduit—Black
Code
NMULTRA –
Available in sizes from 6mm to 53 mm (1/4" to 2") Please contact office for more details.

Non-Metallic Connectors—Straight-Black	Non-Metallic Connectors— 90 Degree-Black
Code	Code
C-NMQLB –	C-NMQLB – 90
Available in sizes from 6 mm to 53 mm (1/4" to 2"). Please contact office for more details	

C (UL) US File No. E19675