


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	STUD SIZE	DIMENSIONS in. [mm]				
		L ± .04 [1,0]	W ± .01 [0,3]	C ± .015 [0,4]	M ± .03 [0,8]	H ± .01 [0,3]
PV10-6RX	#6	1.10 [27,9]	.31 [7,8]	.30 [7,6]	.93 [23,6]	.15 [3,8]
PV10-8RX	#8	1.10 [27,9]	.31 [7,8]	.30 [7,6]	.93 [23,6]	.17 [4,3]
PV10-10RX	#10	1.10 [27,9]	.31 [7,8]	.30 [7,6]	.93 [23,6]	.20 [5,1]
PV10-14RX	1/4"	1.29 [32,8]	.52 [13,2]	.39 [9,9]	1.00 [25,4]	.27 [6,9]
PV10-56RX	5/16"	1.29 [32,8]	.52 [13,2]	.42 [10,7]	1.00 [25,4]	.33 [8,4]
PV10-38RX	3/8"	1.35 [34,3]	.58 [14,7]	.46 [11,7]	1.08 [27,4]	.39 [9,9]

# NOTES:


- USED FOR:
  - #12-10 AWG [4,0-6,0 mm<sup>2</sup>] SOLID OR STRANDED COPPER WIRE
  - 221°F [105°C] MAX. OPERATING TEMPERATURE
  - 600 V. MAX. VOLTAGE RATING  
1000 V. IN SIGNS, FIXTURES & LUMINARIES
- INSTALLATION TOOLS:
  - UL APPROVED: CT-600A (CT-550CH), CT-1550, CT-1551, CT-2550 (CT-2550CH)
  - PANDUIT APPROVED: CT-100A
- WIRE STRIP LENGTH: 5/16" <sup>+1/32</sup> [7,9<sup>+0,8</sup>]
- MATERIAL:
  - STAMPING: .04" [1,0] THK COPPER, TIN PLATED
  - HOUSING: VINYL, YELLOW
- SEE [www.panduit.com](http://www.panduit.com) FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



LISTED  
587H  
E52164



CERTIFIED  
LR31212

										TITLE RING TERMINALS, VINYL EXPANDED INSULATION, #12-10			
										CUSTOMER DRAWING			
										ITEM REVISION NAME N41271BA/06		<div>PANDUIT</div>	
										DATASET FILE NAME N41271BA_DC/06A			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ] .x ± .1 [ 2.54 ]      .xxx ± .005 [ .13 ] .xx ± .01 [ .25 ]      ANGLES ± 5 °			
										<div></div> THIRD ANGLE PROJECTION			
06	10.16.12	JBN	LCA	VMB	REVISED INSTALLATION TOOLS NOTES. UPDATED DRAWING TO CURRENT STANDARDS.	A41271					DRAWING NUMBER: A41271		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY DAW	DATE -	CHK RLS	SCALE N.T.S.	SHT 1 OF 1		SIZE A