

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	STUD SIZE		DIMENSIONS in. [mm]					TOOLS
	ENGLISH	METRIC	L ± [0,76]	W ± [0,25]	C ± [0,51]	M ± [0,76]	H ± [0,25]	
PNF10-6F	#6	M3,5	1.01 [25,65]	.31 [7,87]	.24 [6,10]	.80 [20,32]	.15 [3,81]	*CT-100A *CT-160 *CT-260 *CT-460 CT-600-A (CT-550CH) CT-1550 CT-1551 CT-2500 (CT-2550CH)
PNF10-8F	#8	M4	1.02 [25,91]	.37 [9,40]	.24 [6,10]	.80 [20,32]	.17 [4,32]	
PNF10-10F	#10	--	1.04 [26,42]	.37 [9,40]	.24 [6,10]	.80 [20,32]	.21 [5,33]	
PMNF6-5F	--	M5	1.06 [26,90]	.37 [9,50]	.24 [6,19]	.84 [21,31]	.21 [5,33]	
PNF10-14F	1/4"	M6	1.15 [29,21]	.50 [12,7]	.31 [7,87]	.90 [22,86]	.27 [6,86]	

*PANDUIT APPROVED TOOL

NOTES:

1. cULus LISTED FOR:

- A. 12-10 AWG [4,0-6,0 mm²] STRANDED COPPER WIRE
 B. 221°F [105°C] MAX. OPERATING TEMPERATURE
 C. 600V. MAX. BLDG WIRE
 (1000 V. MAX. IN SIGNS, FIXTURES & LUMINAIRES)


2. SEE www.panduit.com FOR PACKAGE QUANTITIES

3. MATERIAL:

- A. STAMPING: .04" [1,0] THK COPPER, TIN PLATED
 B. HOUSING: VINYL, YELLOW
 C. SLEEVE: BRASS, TIN PLATED

4. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT

5. WIRE STRIP LENGTH: 9/32 ^{+1/32}₋₀ [7,1 ^{+0,8}₋₀]



TITLE			
FORK TERMINALS, NYLON FUNNEL ENTRY, #12-10			
CUSTOMER DRAWING			
ITEM REVISION NAME		N41262BA/10	
DATASET FILE NAME		N41262BA_DC/10A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ± .XX ±		.XXX ± ANGLES ±	
THIRD ANGLE PROJECTION		SEE NOTES	
DRAWING NUMBER:		A41262	
DRAWN BY	DATE	CHK	SCALE
DAW		LCA	N.T.S.
SHT 1 OF 1			SIZE A