

Project Name

Location

Prepared By



SATCO S11271

5.5MR16/GU10/RGB/TW/SF

Notes

[www] 03-22-2021 04:50:55

General

Status	Active
Watts	5.5
Incandescent Equivalent	50
Volts	120V
Shape	MR16
Base	Bi Pin GU10
ANSI Base	GU10
Finish	White
CCT (Kelvin)	2700K-5000K
Temperature	Warm to Cool White/Color Changeable
CRI	80
Lumens	400
Beam Spread	50
Dimmable	Dimmable Only with Starfish App
Hours Rated	25000
Lamp Type	MR
Technology	LED

Smart Product Info

IOT Enabled	Yes
Voice Assistants Supported	Siri; Alexa; Hey Google; SmartThings

Electrical

Operating Frequency	60 Hz
---------------------	-------

Specifications

Dimming Type	Smart
Power Factor	0.7
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	1.97
MOD	2.20
Lens Finish	Clear
Lens Material	Plastic
Weight (lb.)	0.08

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 3 hr per day

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2368910
California Status	Non-Compliant

California Compliant Substitute	S11278
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp