

BQ2 Series


200 A 600 V; standard enclosure


Product specifications

- Conductor range: 6 AWG–250 kcmil
- Aluminum tunnel type connectors for both load and line sides
- For overhead, underground and combination overhead/underground

- Supplied with screw type ring
- Weatherproof Type 3R enclosure
- Primarily used in: All provinces

Note: Supply from an underground network often requires use of stud type connector. Consult your local utility.




	Cat. no	Description	Dimensions (in.)			Weight each	
			H	W	D	lb	kg
	4 Jaw						
	BQ2-V	Overhead, hub opening	15 ⁵ / ₈	8 ⁴⁷ / ₆₄	5 ¹³ / ₃₂	12	5.4
	BQ2-VGN	Overhead opening comes with ground lug on neutral	15 ⁵ / ₈	8 ⁴⁷ / ₆₄	5 ¹³ / ₃₂	12	5.4
	BQ2-VGN-CR	Overhead comes with ground lug on neutral, corrosion resistant	15 ⁵ / ₈	8 ⁴⁷ / ₆₄	5 ¹³ / ₃₂	12	5.4
	BQ2-1 1/2 V	Overhead, hub opening, comes with 1½ in. hub	15 ⁵ / ₈	8 ⁴⁷ / ₆₄	5 ¹³ / ₃₂	12	5.4
	BQ2-2V	Overhead, hub opening, comes with 2 in. hub	15 ⁵ / ₈	8 ⁴⁷ / ₆₄	5 ¹³ / ₃₂	12	5.4
	BQ2-2VGN	Overhead , hub opening comes with 1 ½” hub and ground lug on neutral	15 ⁵ / ₈	8 ⁴⁷ / ₆₄	5 ¹³ / ₃₂	12	5.4
	BQ2-TV	Underground	15 ⁵ / ₈	8 ⁴⁷ / ₆₄	5 ¹³ / ₃₂	12	5.4
	BQ2-TVGN	Underground comes with ground lug on neutral	15 ⁵ / ₈	8 ⁴⁷ / ₆₄	5 ¹³ / ₃₂	12	5.4
	BQ2-TCV	Combination, overhead-underground	15 ⁵ / ₈	8 ⁴⁷ / ₆₄	5 ¹³ / ₃₂	12	5.4
	BQ2-TCV-CR	Combination overhead-underground, corrosion resistant	15 ⁵ / ₈	8 ⁴⁷ / ₆₄	5 ¹³ / ₃₂	12	5.4
	BQ2-TCVGN	Combination overhead-underground comes with ground lug on neutral	15 ⁵ / ₈	8 ⁴⁷ / ₆₄	5 ¹³ / ₃₂	12	5.4
	BQ2-TCVGN-CR	Combination overhead-underground comes with ground lug on neutral , corrosion resistant	15 ⁵ / ₈	8 ⁴⁷ / ₆₄	5 ¹³ / ₃₂	12	5.4
	BQ2-22VNH	Overhead, twin hub opening	15 ⁵ / ₈	8 ⁴⁷ / ₆₄	5 ¹³ / ₃₂	12	5.4
	BQ2-22VNHGN	Overhead , twin hub opening comes with ground lug on neutral	15 ⁵ / ₈	8 ⁴⁷ / ₆₄	5 ¹³ / ₃₂	12	5.4
	BQ2-2VGN-CR	Overhead comes with ground lug on neutral, corrosion resistant	15 ⁵ / ₈	8 ⁴⁷ / ₆₄	5 ¹³ / ₃₂	12	5.4
	BQ2-22V	Overhead, twin hub opening, comes with 2 in. hubs	15 ⁵ / ₈	8 ⁴⁷ / ₆₄	5 ¹³ / ₃₂	12	5.4
	BQ2-22VGN	Overhead, twin hub opening comes with 2 in hubs and ground lug on neutral	15 ⁵ / ₈	8 ⁴⁷ / ₆₄	5 ¹³ / ₃₂	12	5.4
	Factory-installed accessories						
	Include:	-GN	Ground lug on neutral				
		-5	5 th jaw standard capacity				
		-6	5 th jaw full capacity, 6 o'clock position				

BQ2 Series


200 A 600 V; standard enclosure

Diagrams



200 A 600 V; standard enclosure

- Conductor range: 6 AWG–250 kcmil
- Aluminum tunnel type connectors for both load and line sides

-  Approved for copper
or aluminum

Trade size knockout
1 1/4, 1 1/2, 2
and 2 1/2 in.
3 sets

Trade size knockout
1/2 in.

Trade size knockout
1/4 in.

2 1/16 in.


1 1/16 in.

3 1/16 in.

1 1/16 in.

3 1/16 in.

12 in.



BS2 Series


200 A 600 V; oversize enclosure


Product specifications

- Conductor range: 6 AWG–250 kcmil
- Aluminum tunnel type connectors for both load and line sides
- For overhead, underground and combination overhead/underground

- Supplied with screw type ring
- Weatherproof Type 3R enclosure
- Primarily used in: B.C., AB, Sask., Man., Ont., N.S.

NOTE: Supply from an underground network often requires use of stud type connector. Consult your local utility.




	Cat. no.	Description	Dimensions (in.)			Weight each	
			H	W	D	lb	kg
	4 Jaw						
	BS2-V	Overhead, hub opening	17⅞	12	5⅛	14	6.3
	BS2-INV	Overhead , hub opening comes with insulated neutral	17⅞	12	5⅛	14	6.3
	BS2-1 1/2 V	Overhead, hub opening, comes with 1½ in. hub	17⅞	12	5⅛	14	6.3
	BS2-2V	Overhead, hub opening, comes with 2 in. hub	17⅞	12	5⅛	14	6.3
	BS2-TV	Underground	17⅞	12	5⅛	14	6.3
	BS2-INTV	Underground comes with isolated neutral	17⅞	12	5⅛	14	6.3
	BS2-TCV	Combination, overhead-underground	17⅞	12	5⅛	14	6.3
	BS2-INTCV	Combination overhead-underground comes with isolated neutral	17⅞	12	5⅛	14	6.3
	BS2-TCVGN	Combination overhead-underground comes with ground lug on neutral	17⅞	12	5⅛	14	6.3
	BS2-TCVBC	Combination, overhead-underground comes with 3" ko	17⅞	12	5⅛	14	6.3
	BS2-TCVBC-CR	Combination overhead-underground comes with 3" ko	17⅞	12	5⅛	14	6.3
	BS2-TCVBCGN	Combination overhead-underground comes with ground lug on neutral	17⅞	12	5⅛	14	6.3
	BS2-22VNH	Overhead, twin hub opening	17⅞	12	5⅛	14	6.3
	BS2-22V	Overhead, twin hub opening, comes with 2 in. hubs	17⅞	12	5⅛	14	6.3
	BS2-9V	Overhead, hub opening, comes with 5 th jaw, 9 o'clock and insulated neutral	17⅞	12	5⅛	14	6.3
	Factory-installed accessories						
	Include: -5	5 th jaw, standard capacity, 9 o'clock position					
	-6	5 th jaw, full capacity, 6 o'clock position					
	-9	5 th jaw, full capacity, 9 o'clock position					
	-IN	Insulated neutral					
	-GN	Ground lug on neutral					

BS2 Series

200 A 600 V; oversize enclosure

Diagrams



BS2 Series kit


200 A 600 V; oversize enclosure with PVC accessories


Product specifications

- Conductor range: 6 AWG–250 kcmil
- Aluminum tunnel type connectors for both load and line sides
- For overhead, underground and combination


- Supplied with screw type ring
- Weatherproof Type 3R enclosure
- Primarily used in: Ontario only

Note: Supply from an underground network often requires use of stud type connector. Consult your local utility.



	Cat. no.	Description	Qty.
	Kit		
	BS2-TCV-KIT2U	Kit – Meter socket with PVC accessories	
	Consists of		
	BS2-TCV	200 A meter socket	1
	E943J	2 in. Terminal adaptor	1
	E986J	2 in. LB access fitting	1
	E995J	2 in. Meter offsets	2
	E977JC	2 in. Clamps	2
	UA9AJCB-CTN	2 in. Elbow 90°	1
	CI1716	2 in. Nut	3
	PH20	2 in. Hub	1

Diagrams




200 A, 120/240; single-phase service

- Line #6 AWG to 350 kcmil, load 2 x #6-4/0 AWG
- Tunnel type connectors for both load and line sides
- For underground and above ground service
- Weatherproof Type 3R enclosure



- Application: When distance is a factor, larger conductors require larger connectors.



	Cat. no.	Description	Dimensions (in.)			Weight Each	
			H	W	D	lb	kg
	4 Jaw						
	BS2-TCVFA	Combination overhead and underground 200 A service	27 ¹ / ₁₆	12	5 ⁷ / ₁₆	14	6.3

Technical drawing of a vertical pipe with the following dimensions and specifications:

- Top flange width: $5\frac{1}{16}$ in.
- Top flange height: $1\frac{1}{32}$ in.
- Main body height: $27\frac{7}{16}$ in.
- Bottom flange height: $5\frac{7}{8}$ in.
- Knockout diameter: $2\frac{1}{8}$ in.
- Knockout specification: Trade size knockout 1 in., $1\frac{1}{4}$ in., $1\frac{1}{2}$ in., 2 in., $2\frac{1}{2}$ in. 2 places
- Overall height: 10.61 in.





BS2L Series

200 A 600 V; oversize enclosure lay-in lug


Product specifications

- Same as BS2 series with the exception that lay-in type connectors are provided
 - Conductor range: 6 AWG–250 kcmil
 - Aluminum lay-in type connectors for both load and line sides
- For overhead, underground and combination overhead/underground
 - Supplied with screw type ring
 - Weatherproof Type 3R enclosure
 - Primarily used in: B.C., Ont.



	Cat. no.	Description	Dimensions (in.)			Weight each	
			H	W	D	lb	kg
	4 Jaw						
	BS2L-TV	200 A underground with lay-in lugs	17 ¹ / ₈	12	5 ¹ / ₁₆	16	7.2
	BS2L-INTV	200 A underground with lay in lug, insulated neutral	17 ¹ / ₈	12	5 ¹ / ₁₆	16	7.2
	BS2L-TCV	200 A over/under combination with lay-in lugs	17 ¹ / ₈	12	5 ¹ / ₁₆	16	7.2
	BS2L-INTCV	200 A overhead-underground with lay in lugs, isolated neutral	17 ¹ / ₈	12	5 ¹ / ₁₆	16	7.2
	BS2L-TCVGN	200 A underground-overhead with lay in lugs comes with ground lug on neutral	17 ¹ / ₈	12	5 ¹ / ₁₆	16	7.2
	BS2L-TCVBCR	200 A over/under combination with lay-in lugs (BC Hydro)	17 ¹ / ₈	12	5 ¹ / ₁₆	16	7.2
Factory-installed accessories							
Include: -5		5 th jaw standard capacity					
-6		5 th jaw full capacity, 6 o'clock position					
-9		5 th jaw full capacity, 9 o'clock position					
-IN		Insulated neutral					

Diagrams




BS2M Series

200 A 600 V; oversize enclosure, subfeed on load side

Product specifications


- Conductor range: line: 6 AWG–250 kcmil, load: 12–1/0 AWG
 - Aluminum tunnel type connector for line side
 - For overhead service only
- Dual lug subfeed for load side
 - Supplied with screw type ring
 - Weatherproof Type 3R enclosure
 - Primarily used in: All provinces



	Cat. no.	Description	Dimensions (in.)			Weight each	
			H	W	D	lb	kg
	4 Jaw						
BS2M-V	BS2M-V	Overhead, hub opening	17 ¹ / ₈	12	5 ⁷ / ₁₆	15	6.8



Diagrams





MO2 Series

200 A 600 V; underground only




Product specifications

- Conductor range: line: single ½ in. studs to accommodate compression lugs 350 kcmil max. (supplied by utility), load: 6 AWG–250 kcmil
 - For underground service only
- Aluminum tunnel type connectors for load side, ½ in. studs on line side
 - Supplied with screw type ring
 - Weatherproof Type 3R enclosure
 - Primarily used in: Sask., Man., Ont., Que.



	Cat. no.	Description	Dimensions (in.)			Weight each	
			H	W	D	lb	kg
	4 Jaw						
	MO2-V	Underground ½ in. studs	19⅞	12	5⅞ ¹⁶	18	8.1
	MO2-INV	Underground ½ in. stud comes with isolated neutral	19⅞	12	5⅞ ¹⁶	18	8.1
	MO2-VO	Underground ½ in. studs for Ontario	19⅞	12	5⅞ ¹⁶	18	8.1
	MO2-INV0	Underground ½ in. stud for ontario comes with isolated neutral	19⅞	12	5⅞ ¹⁶	18	8.1
	Factory-installed accessories						
Include: -M			2/0 AWG subfeed on load side				

Diagrams





MO2 Series Kit

200 A 600 V; underground only with PVC accessories


Product specifications

- Conductor range: line: single ½ in. studs to accommodate compression lugs (supplied by utility), load: 6 AWG–250 kcmil
 - For underground service only
- Aluminum tunnel type connectors for load side
 - Supplied with screw type ring
 - Weatherproof Type 3R enclosure
 - Primarily used in: Ontario only

 Approved for copper or aluminum

	Cat. no.	Description	Qty.
	Kit		
	MO2-VO-KIT2U	Kit – Meter socket with PVC accessories	
	Consists of		
	MO2-VO	200 A meter socket	1
	CI1716	2 in. Locknut	3
	E943J	2 in. Male adaptor	1
	E977JC	2 in. Pipe strap	2
	E986J	2 in. Conduit bodies – LB type	1
	E995J	2 in. Meter offsets	2
	UA9AJCB-UPC	2 in. 90° Elbow	1

Diagrams




MO2 Series kit

200 A 600 V; underground only with PVC accessories

Product specifications

- Conductor range: line: single ½ in. studs to accommodate compression lugs (supplied by utility), load: 6 AWG–250 kcmil
 - For underground service only
- Aluminum tunnel type connectors for load side, ½ in. studs on line side
 - Supplied with screw type ring
 - Weatherproof Type 3R enclosure
 - Primarily used in: Quebec only

 Approved for copper or aluminum





MO2-V-KIT1-1/4U

Cat. no.	Description	Qty.
Kit		
MO2-V-KIT1-1/4U	Meter socket with PVC accessories	
Consists of		
MO2-V	200 A Meter socket	1
CE942RL	3 in. PVC/DB2 adaptor	1
CI1710	1¼ in. Nut	2
CI1724	3 in. Nut	1
CI-DUCT-1	Duct seal	1
E943G	1¼ in. Male adaptor	2
E943L	3 in. Male adaptor	1
E945L	3 in. Expansion fitting	1
E977GC	1¼ in. Pipe strap	1
E977LC-CAR	3 in. Pipe strap	1
E986G	1¼ in. Conduit bodies – LB type	1
UA9AGCB-UPC	1¼ in. 90° Elbow	1

Cat. no.	Description	Qty.
Kit		
MO2-V-KIT2U	Meter socket with PVC accessories	
Consists of		
MO2-V	200 A Meter socket	1
CE942RL	3 in. PVC/DB2 adaptor	1
CI1716	2 in. Nut	2
CI1724	3 in. Nut	1
CI-DUCT-1	Duct seal	1
E943J	2 in. Male adaptor	2
E943L	3 in. Male adaptor	1
E945L	3 in. Expansion fitting	1
E977JC	2 in. Pipe strap	1
E977LC-CAR	3 in. Pipe strap	1
E986J	2 in. Conduit bodies – LB type	1
UA9AJCB-UPC	2 in. 90° Elbow	1

Diagrams



MO2-V bottom