



NVENT CADDY CAT CM DOUBLE J-HOOK, 70 CABLE CAPACITY, CAT 5E, 30 CABLE CAPACITY, CAT 6A

CATALOG NUMBER

CAT100CM



CERTIFICATIONS



FEATURES

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

System offers a convenient pathway for wires and cables

Double J-Hooks can be mounted vertically along the same drop rod to create a tree configuration

Allows addition of cables even when fixed flush to overhead decking

Specially designed double J-Hook has large-diameter, rounded support surfaces

Rounded edges help prevent over-bending and kinking of cables

Ideal for retrofit applications where cable runs need to be routed around existing building infrastructure

Compliant with NEC® and ANSI®/TIA structured cabling systems standards

PRODUCT ATTRIBUTES

Material: Steel

Finish: Electrogalvanized

Cable Capacity, Cat 5e: 70

Cable Capacity, Cat 6: 50

Cable Capacity, Cat 6A: 30

A: 7 1/4"


Area: 3.16 in²

Hole Size: 3/8"

ADDITIONAL PRODUCT DETAILS

Area shown is the combined value for both sides. Divide by 2 for area of each side.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.