### **Battery Connector Crimp Tools**

- Available with Shure Stake® mechanism to ensure a complete crimp every time (BCT840S)
- Crimps casting and tubular battery connectors ranging from 4 AWG to 4/0
- Heavy-duty crimping tool including die for 8 AWG-4/0 battery connectors, lugs and splices
- The single die is an integral part of the tool; no dies to lose or misplace

Cat. No.	Description	Pkg. Qty.
BCT840	Adjustable Dieless Crimp Tool for cast and tubular battery connectors	
BCT840S	Adjustable Dieless Crimp Tool with Shure Stake® mechanism for cast and tubular battery connectors	1
TBM5V	Ratchet Crimp Tool with die for 8 AWG to 4/0 battery connectors	
TBM5SV	Ratchet Crimp Tool with Shure Stake® and die for 8 AWG to 4/0 battery connectors	





### **BCS8-40 Battery Cable Stripper**



Cat. No.	Description	Pkg. Qty.
BCS8-40	Cable stripper for 8 AWG-4/0 battery cable with replacement blade provided in the handle	1

## 368-CK Cable Stripper



Cat. No.	Description	Pkg. Qty.
368-CK	Cable stripper for #1 to 1,000 kcmil	1

## 364RF/366RF Cable Cutters with Fiberglass Handles

Cat. No.	Description	Pkg. Qty.
364RF	Cutter for up to 500 kcmil copper and aluminum	
366RF	Cutter for up to 1,000 kcmil copper and aluminum	

For copper and aluminum cable only. Not for steel.





# TBM40HC Hand-Operated Hydraulic Cutting Tool

- Specifically designed to cut copper, aluminum and telecommunications cables up to 3.35 in. 0.D.
- Offers dual-speed action: fast advancing speed for rapid approach of blades to cable and slower, more powerful speed for cutting
- Blades manufactured from high-strength, heat-treated steel to ensure long service life
- Head easily opens to enable cutting of existing run cables
- Head rotates 180°, enabling operator to position for easiest use
- Automatic safety valve bypasses hydraulic system when reaching maximum pressure
- Pressure release device can also be activated during any point of operation

Cat. No.	Description	Pkg. Qty.
ТВМ40НС	Hand-operated hydraulic cutting tool	1



### **CSR750 Cable Cutter**

- Special advance stroke mechanism requires less handle force
- Cuts copper or aluminum cables up to 750 kcmil
- · Short handles (only 10 in. long) enable use in tight spaces

Cat. No.	Description	Pkg. Qty.
CSR750	Cutter for up to 750 kcmil copper or aluminum	1



# Li Cutter for Up to 1500 kcmil Al

- · Designed for one-handed control of blade advancement and retraction
- Cuts up to 1000 kcmil copper and 1500 kcmil aluminum 2-1/8 in. 0.D. aluminum ( not for use on ACSR)

#### **Specifications**

- Capacity: Cu 1000 kcmil, Al 1500 kcmil (ACSR – do not cut)
- Dimensions (L x W x H): 16 in. x 4.5 in. x 5 in.
- Battery: 14.4 VDC
- Weight with Battery: 5.8 lb.

Cat. No.	Description	
TBM54CT-LI	Li cutter for up to 1500 kcmil Cu	





## Li Cutter for 750 kcmil Cu, 636 kcmil ACSR

- Designed for one-handed control of blade advancement and retraction
- Cuts up to 750 kcmil copper and 2-1/8 in. O.D. aluminum and 636 kcmil ACSR

#### **Specifications**

- Capacity: Cu 750 kcmil, Al 1500 kcmil, ACSR 636 kcmil
- Dimensions (L x W x H): 16 in. x 4.5 in. x 5 in.
- Battery: 14.4 VDC
- . Weight with Battery: 5.8 lb.

Cat. No.	Description
TBM54CTS-LI	Li cutter for 750 kcmil Cu, 636 kcmil ACSR

### Li Cutter for steel, ACSR, Al, Cu

- Designed for one-handed control of blade advancement and retraction
- · Rotating head to allow maximum flexibility for cutting
- Features a two-stage rapid advance ram for reduced cycles with overload bypass protection, which will pop off if the material is beyond the cutter's capacity
- Cuts up to 1-1/2 in. O.D. Copper, Aluminum and ACSR cable
- Cuts rebar, ground rod up to 5/8 in. and wire rope up to 3/4 in.
- 14.4 V DC



Cat. No.	Description	Pkg. Qty.
TBM58PCTS-LI	Li cutter for steel, ACSR, AI, Cu	1

## 297-32136 Hydraulic Cutting Head

- · Heavy-duty cutter with high strength steel blades
- Cuts both aluminum and copper wire to 1-1/2 O.D.

· Cutter supplied with carrying case

Weight with Battery: 14.6 lb.

#### **Specifications**

- Max. Cutting Capacity (aluminum and copper): 1-1/2 in. 0.D.
- Dimensions (L x W x H): 14-1/2 x 2-1/2 in. x 4 in.
- Weight: 8.5 lb.



Cat. No.	Description	Pkg. Qty.
297-32136	Hydraulic Cutting Head	1

## TBM40HCRH Hydraulic Cutting Head

- Heat-treated, high-strength steel blades for clean cuts and long service life
- Quick automatic coupler speeds connection to hydraulic systems
- · Cutter supplied with carrying case



 Max. Cutting Capacity (copper, aluminum and telecommunications cable): Up to 3.35 in. 0.D.\*

- Hydraulic Operating Pressure: 10,000 psi (maximum)
- Dimensions (L x W): 15.94 in. x 5.63 in.
- Weight: 10.8 lb.

\* Not designed for cutting steel-reinforced conductors



Cat. No.	Description	Pkg. Qty.
TBM40HCRH	Hydraulic Cutting Head	1

