



LED BR30

7.2BR30/PER/922-27/P/E26/WG 6/1FB

Philips BR30 LED lamps are the smart alternative to standard incandescent. The traditional lamp design can provide excellent dimming performance with spectular energy savings. They provide the beautiful light and dependable performance you expect from LED at an economical price.

Product data

E26 [Single Contact Medium Screw]
Yes
15000 h
50000X
7.2-65W
922-927 [CCT of 2200K-2700K]
90°
650 lm
Warm White (WW)
- K
90.00 lm/W
<4
90
70 %
60 Hz
7.2 W
85 mA
65 W


Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	75 °C
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb Finish	Frosted
Bulb Shape	BR30 (BR30)
Approval and application	
Energy Consumption kWh/1000 h	- kWh
Product data	
Order product name	7.2BR30/PER/922-27/P/E26/WG 6/1FB
EAN/UPC - Product	046677457044
Order code	929001870334
Numerator - Quantity Per Pack	1

Datasheet, 2022, January 11 data subject to change

LED BR30

Numerator - Packs per outer box	6
Material Nr. (12NC)	929001870334
Net Weight (Piece)	0.100 kg


Dimensional drawing





7.2BR30/PER/922-27/P/E26/WG 6/1FB

Product D C 7.2BR30/PER/922-27/P/E26/WG 6/1FB 95 mm 132 mm


Photometric data








LEDBulbs BR30 120V 19-120W 1200lm 2700K E26 D




LEDBulbs BR30 120V 19-120W 1200lm 2700K E26 D

LED BR30

Lifetime





LEDBulbs BR30 120V 19-120W 1200lm 2700K E26 D

LEDBulbs BR30 120V 19-120W 1200lm 2700K E26 D



© 2022 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.