

Project:		Type:
Drawn by:	Catalogue #:	Date:

Individual Spec Sheet

TRADITIONAL

LED CEILING LUMINAIRE

5 CCT Selectable

ORDERING INFORMATION

Order code: 68973

Model number: CLTD14-R24W-A-5CWH UPC: 069549022980

Case quantity:

PHYSICAL DATA

Dimensions in. (mm): 13 3/4" (350) Shape: Round **Housing material:** Steel **Housing finish:** White Lens material: Polystyrene Lens finish: Frosted Mounting: Surface

PERFORMANCE DATA

Watts (W): 24 Volts (VAC): 120

Colour temperature (K)1: 2 700/3 000/3 500/4 000/5 000

1 800 Lumen output (lm)2: Efficiency (Im/W): 75 CRI: 80 Life L70 (h)3: 50 000 Beam angle (°): 110 **Dimming:** Yes Power factor: >0.70 Frequency (Hz): 60

Operating temp. range: -10°C to 40°C (14°F to 104°F)

LUMEN SPECIFICATION TABLE

Order		Model number	2 700 K		3 000 K		3 500 K		4 000 K		5 000 K	
C	code		Lumen output (Im)	Efficiency (Im/w)								
6	8973	CLTD14-R24W-A-5CWH	1 812	75	1 816	76	1 924	80	1 974	82	1 987	83

DEFAULT PROGRAMMING

3 000 K

ACCESSORIES (order separately)

Order code	Model number	Type	Finish	Diameter (in.)	Case qty (master)
68976	LEN-CLTD14	Lens	Frosted	13 3/4	5

This lighting equipment meets requirements of ICES-005 issue 5 class B for use in residential applications Data is based upon tests performed in a controlled environment.

Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.



























¹ Typical colour temperature range: +/- 5 %

² Lumen values are derived from Energy Star reported data. Initial lumens range: +/- 10 %

³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations




COMPATIBLE DIMMERS¹

Brand	Model
LEGRAND	RH703PTUTC
COOPER	AAL06, SAL06P3
LEVITON	IPL06, DSL06-1ZL, DSM10-1LZ, DDMX1
LUTRON	PD-5NE, PD-6WCL, RRD-6NA-WH, DVCL-153P, CTCL-153P, DVCL-253P, AYCL-253P, DVRP- 253-WH, SELV-300P, MACL-153P

Dimming range: 0-10%

¹ This table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Some dimmers may require more than one product for stable operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation.


DIMENSIONS AND WEIGHT



PHOTOMETRIC DATA¹

68973 • CLTD14-R24W-A-5CWH • 24 W • 3 000 K • 1 816.1 lm


Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	347.2	19.1
0-40	575.7	31.7
0-60	1 049.7	57.8
60-90	509.3	28
70-100	388.9	21.4
90-120	173.9	9.6
0-90	1 558.9	85.8
90-180	257.1	14.2
0-180	1 816.1	100

Illuminance at a distance



Qty	Description	Price	
Name:	tions of the luminaire configuration mentioned above.		
Company:			
Signature:		Date:	

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.



¹ Complete IES files available on our website.