

Project: _____ Type: _____
 Drawn by: _____ Catalogue #: _____ Date: _____

Individual Spec Sheet

WCI-L

MINI WALL PACK

Selectable color temperature (4 000 K / 4 500 K / 5 000 K)
 Integrated Photocell

ORDERING INFORMATION

Order code: 68312
Model number: WCI-LS2-W/3C-BR
UPC: 069549015906
Case quantity: 10

PHYSICAL DATA

Dimensions: 5.79" x 8.58" x 3.07"
Housing Material: Aluminum die-cast
Lens type: Polycarbonate frosted lens
Mounting: Surface mount to a junction box or use with surface conduit.
Photocell: Integrated 120-277 V photocell which can easily be disabled.

PERFORMANCE DATA


Watts (W): 20
Volts (VAC): 120-277
Color temperature (K):¹ 3CCT (4 000 K / 4 500 K / 5 000 K)
Lumen output (lm):² 2 522 / 2 926 / 2 637
Efficiency (lm/W): 127
CRI: 80
Finish: Bronze
Dimming (Yes/No): No
LED current (mA): 310
Power factor: 0.94
Frequency (Hz): 50/60
THD (%): 13
Operating temp. range: -40°C to 40°C

¹ Typical color temperature range: +/- 5 %

² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %

³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations

SELECTABLE COLOR TEMPERATURE SWITCH




This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.
 Data is based upon tests performed in a controlled environment.
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.




Not all products are qualified on the DLC QPL. To view our DLC qualified products, please consult the DLC Qualified Products List at www.designlights.org/search.

DIMENSIONS

FRONT




SIDE

PHOTOMETRIC DATA¹

68312 • WCI-LS2-W-3C-BR (4000K) • 2 520.9 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Luminaire
0-30	640.2	25.4%
0-40	988.5	39.2%
0-60	1 660.3	65.9%
60-90	619.3	24.6%
70-100	414.9	16.5%
90-120	182.0	7.2%
0-90	2 279.6	90.4%
90-180	241.3	9.6%
0-180	2 520.9	100%

Illuminance at a distance

	Center beam fc	Beam width
8.3'	12.3 fc	18.4' 20.5'
16.7'	3.03 fc	36.9' 41.2'
25.0'	1.35 fc	55.3' 61.6'
33.3'	0.76 fc	73.7' 82.1'
41.7'	0.49 fc	92.3' 102.8'
50.0'	0.34 fc	110.6' 123.3'

■ Vert. spread: 95.8°
■ Horiz. spread: 101.9°

¹ Complete IES files available on our website.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____

Company: _____

Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions.
All products are subject to change or may be discontinued any time without notice.