

5MP HDCVI Fixed Dome Camera

Starlight IR Camera with 16:9 Aspect Ratio



HDCVI



- 1/2.7-in. 5 MP Progressive-scan CMOS Sensor
- 5 MP (2880 x 1620) at 25 fps Maximum Resolution
- 2.8 mm Fixed Lens
- 16:9 Aspect Ratio for no Image Stretching
- Starlight Technology for Low-light Applications
- True Wide Dynamic Range (120 dB) and 3D Noise Reduction
- HDCVI, AHD, TVI, or CVBS Output, Switchable
- Maximum IR Length 30 m (98.43 ft), Smart IR
- ArcticPro Series Camera - Operational down to -40°C (-40°F)
- IP67 Ingress Protection and IK10 Vandal Resistance
- Five-year Warranty*



System Overview

Experience the superior clarity of Dahua's 5 MP HDCVI cameras for vast coverage and superior image details. The 5 MP HDCVI series leverages existing coax infrastructures to deliver forensic-level images seamlessly and over long distances. The HDCVI camera offers multiple output formats that are easily switchable and a 16:9 aspect ratio. With a 16:9 format, images maintain a true, undistorted view without stretching, a feature not found on many 5MP HD over coax cameras. The camera is suitable for most applications, offering IR illumination for difficult lighting conditions, input voltage tolerance for inconsistent power supplies, and IP67 certification for operation in harsh outdoor environmental conditions.

Functions

Starlight Technology

For challenging low-light applications, Dahua's Starlight Ultra-low Light Technology offers best-in-class light sensitivity, capturing details in low-light applications. The camera uses a set of optical features to balance light throughout the scene, resulting in clear images in dark environments.

Long Distance Transmission

HDCVI technology guarantees real-time transmission over long distances without loss of video quality. HDCVI cameras provide the same resolution as most IP network camera systems using existing RG-59, RG-6, or CAT 6 UTP cabling.

Simplicity

HDCVI technology seamlessly integrates traditional analog surveillance systems with upgraded, high-quality HD video, making it the best choice to protect security investments. The plug and play approach enables full HD video surveillance without the hassles of configuring a network.

Smart IR

With IR illumination, detailed images can be captured in low light or total darkness. The camera's Smart IR technology adjusts the intensity of the camera's infrared LEDs to compensate for the distance of an object. Smart IR technology prevents IR LEDs from whitening out images as they come closer to the camera. The camera's integrated infrared illumination provides high-performance in extreme low-light environments.

Multiple-format Support

The camera supports multiple video formats including, HDCVI, CVBS, AHD, and TVI. The camera can switch between these four formats via the OSD menu or the switch located on the video output cable, making the camera compatible with not only HDCVI DVRs but also most existing HD/SD DVRs.

ArcticPro

The Dahua ArcticPro Series of extreme-environment cameras combine temperature-tolerant components with a waterproof enclosure to ensure flawless operation in temperatures as low as -40°C (-40°F) without the need for an internal heater. The lack of a heater reduces the camera's power consumption and saves operating costs. For applications that demand high-resolution video with advanced features in extremely cold environments, the Dahua ArcticPro Series offers a camera to satisfy the most demanding requirements.

True Wide Dynamic Range

The camera achieves vivid images, even in the most intense contrast lighting conditions, using industry-leading wide dynamic range (WDR) technology. For applications with both bright and low lighting conditions that change quickly, True WDR (120 dB) optimizes both the bright and dark areas of a scene at the same time to provide usable video.

Protection

The camera is subjected to rigorous dust and water immersion tests and certified to the IP67 Ingress Protection rating making it suitable for demanding outdoor applications. The camera allows for $\pm 30\%$ input voltage tolerance, suitable for the most unstable conditions for outdoor applications, and its 4KV lightning rating provides effective protection for both the camera and its structure against lightning.

Technical Specification

Camera

Image Sensor	1/2.7-in. CMOS Sensor
Effective Pixels	2880 (H) x 1620 (V), 5 MP
Aspect Ratio ¹	16:9
Scanning System	Progressive
Electronic Shutter Speed	1/4 s to 1/100,000 s
Minimum Illumination	Color: 0.001 lux at F1.6, 30 IRE 0 lux with IR on
S/N Ratio	More than 65 dB
IR Distance	Up to 30.0 m (98.43 ft)
IR On/Off Control	Auto, Manual
IR LEDs	12

Lens

Lens Type	Fixed-focal
Mount Type	M12
Focal Length	2.8 mm
Maximum Aperture	F1.6
Angle of View	Horizontal: 111° Vertical: 58° Diagonal: 132°
Iris Type	Fixed
Close Focus Distance	900 mm (35.43 in.)

Installation Angle

Range	Pan: 0° to 355° Tilt: 0° to 65° Rotation: 0° to 355°
-------	--

DORI Distances²

Detect (8 ppf)	Observe (19 ppf)	Recognize (38 ppf)	Identify (76 ppf)
63.60 m (208.70 ft)	25.40 m (83.30 ft)	12.70 m (41.70 ft)	6.40 m (21.0 ft)

Video

Resolution Output	5 MP (2880 x 1620), 4 MP (2560 x 1440), 1080p (1920 x 1080), 720p (1280 x 720), 960H (960 x 480), D1 (704 x 480), CIF (352 x 240)		
Maximum Frame Rate	HDCVI	5 MP at 25 fps, 4 MP at 30 fps, 1080p at 30 fps	
	AHD	4 MP at 30 fps	
	TVI	4 MP at 30 fps	
	CVBS	960H	
Video Output	One (1) BNC Output, HDCVI, AHD, TVI, CVBS switchable		

Video Transmission ³	RG-59/U Coax	720p: 800 m (2624.67 ft) 1080p: 500 m (1640.42 ft) 5 MP: 500 m (1640.42 ft)
	RG-6/U Coax	720p: 1200 m (3937.01 ft) 1080p: 800 m (2624.67 ft) 5 MP: 700 m (2296.59 ft)
	CAT 6 UTP (balun required)	720p: 450 m (1476.38 ft) 1080p: 300 m (984.25 ft) 5 MP: 300 m (984.25 ft)
Day/Night	Auto (ICR)	
OSD Menu	Multi-language	
BLC Mode	BLC, HLC, HLC-Pro, True WDR	
WDR	120 dB	
Gain Control	Auto, Manual	
Noise Reduction	3D NR	
White Balance	Auto, Manual	
Advanced Features	Smart IR Mirror	
Privacy Masking	Off, On (8 Areas, rectangular)	

Certifications

CE	EN55032:2015, EN 61000-3-2:2014, EN 61000-3-3:2013, EN55024:2010+A1:2015, EN 55035:2017, EN50130-4:2011+A1:2014,
Safety	UL60950-1 EN 62368-1:2014+A11:2017 CAN/CSA C22.2 No.60950-1
Electromagnetic Compatibility (EMC)	CFR 47 FCC Part 15 subpart B ANSI C63.4-2014

Electrical

Power Supply	12 VDC ±30%
Power Consumption	Maximum 4.5 W (12 VDC, IR on)

Environmental

Operating Conditions	-40° C to +60° C (-40° F to +140° F) Less than 95% RH, non condensing
Storage Conditions	-40° C to +60° C (-40° F to +140° F) Less than 95% RH, non condensing
Ingress Protection	IP67
Vandal Resistance	IK10

Construction

Casing	Plastic and Metal
Dimensions	ø109.90 mm x 81.0 mm (ø4.33 in. x 3.19 in.)
Net Weight	0.33 kg (0.73 lb)
Gross Weight	0.47 kg (1.04 lb)

1. To view the 16:9 video output on a Dahua HDCVI DVR you must update the DVR to the latest firmware. Obtain the latest firmware on the Dahua Wiki at <https://dahuawiki.com/Recorders>.

2. The DORI distance is a measure of the general proximity for a specific classification to help pinpoint the right camera for your needs. The DORI distance is calculated based on sensor specifications and lab test results according to EN 62676-4, the standard that defines the criteria for the Detect, Observe, Recognize and Identify classifications.

3. Transmission distance results verified by real-scene testing in Dahua's test laboratory. Actual transmission distances may vary due to external influences, cable quality, and wiring structures.

Ordering Information


Type	Part Number	Description
5 MP HDCVI Camera	A52BL62	5 MP Starlight HDCVI IR 2.8 mm Fixed Lens Dome Camera, 16:9 Aspect Ratio
Accessories, optional	DH-PFA109	Mount Adapter
	PFA117	Extension Pole for PFB220C
	PFA123	Waterproof Junction Box
	PFA136	Junction Box
	PFA150	Pole Mount (Use with DH-PFA109 and PFB305W)
	PFA151	Corner Mount (Use with DH-PFA109 and PFB305W)
	PFA152-E	Pole Mount (Use with PFA136 or PFB203W)
	DH-PFA200G	Gang Box Adapter
	PFA200W	Sun/Rain Shield
	PFB203W	Wall Mount (Use alone or with PFA152-E pole mount)
	PFB220C	Ceiling Mount (Use with DH-PFA109 mount adapter)
	PFB305W	Wall Mount (Use alone or with PFA150 or PFA151)
	DH-PFM321D-US	12 VDC, 1 A Power Adapter
DH-PFM800-4K	4K Passive HDCVI Balun	

Accessories

Optional:



Mounting Diagram



Dimensions (mm/in.)

