

# PSR16-600-70

## General Information

<b>Extended Product Type:</b>	PSR16-600-70
<b>Product ID:</b>	1SFA896107R7000
<b>EAN:</b>	7320500338261
<b>Catalog Description:</b>	SOFTSTARTER
<b>Long Description:</b>	Softstarter PSR16-600-70 for max 600V main voltage and 100-240V 50/60Hz control supply voltage



## Categories

Products » Low Voltage Products and Systems » Control Products » Softstarters » Softstarters

## Ordering

<b>EAN:</b>	7320500338261
<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	85371099

## Dimensions

<b>Product Net Width:</b>	45.000 mm
<b>Product Net Height:</b>	140.000 mm
<b>Product Net Depth:</b>	114.000 mm
<b>Product Net Weight:</b>	0.4 kg

## Container Information

<b>Package Level 1 Width:</b>	51 mm
<b>Package Level 1 Length:</b>	156 mm
<b>Package Level 1 Height:</b>	124 mm
<b>Package Level 1 Gross Weight:</b>	0.55 kg
<b>Package Level 1 EAN:</b>	7320500338261
<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 2 Units:</b>	1 piece

## Technical

<b>Rated Operational Voltage:</b>	Main Circuit 208 ... 600 V AC
<b>Rated Control Supply Voltage (U<sub>s</sub>):</b>	100 ... 240 V AC
<b>Rated Control Circuit Voltage (U<sub>c</sub>):</b>	50 Hz / 60 Hz 100 ... 240 V AC
<b>Rated Frequency (f):</b>	Main Circuit 50/60 Hz Control Supply 50/60 Hz
<b>Rated Operational Power - In-Line Connection (P<sub>e</sub>):</b>	at 230V 4 kW at 400V 7.5 kW at 500V 7.5 kW
<b>Rated Operational Current - In-Line Connection (I<sub>e</sub>):</b>	16 A
<b>Service Factor Percentage:</b>	100 %

<b>Overload Protection:</b>	Recommended MS132 10.00 ... 16.00
<b>Integrated Electronic Overload:</b>	No
<b>Adjustable Rated Motor Current Ie:</b>	No %
<b>Starting Capacity at Maximum Rated Current Ie:</b>	4xIe for 6s
<b>Ramp Time:</b>	During Start 1 ... 10 second(s) During Stop 0 ... 20 second(s)
<b>Initial Voltage During Start:</b>	40 ... 70 %
<b>Step Down Voltage Special Ramp:</b>	100...60 %
<b>Current Limit Function:</b>	No
<b>Switch for Inside Delta Connection:</b>	No
<b>Run Signal Relay:</b>	Yes
<b>By-pass Signal Relay:</b>	No
<b>Fault Signal Relay:</b>	No
<b>Overload Signal Relay:</b>	No
<b>Signal indication completed start ramp (LED):</b>	Green
<b>Signal indication ready to start/standby ON (LED):</b>	Green
<b>Signal indication running R (LED):</b>	Green
<b>Signal indication ramping up/down (LED):</b>	Green
<b>Number of Starts Per Hour at 3.5*Ie for 7 sec. 50% ON Time 50% OFF Time:</b>	10
<b>Communication:</b>	FiledBusPlug(Optional)
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Terminal Type:</b>	Screw Terminals
<b>Connecting Capacity-Main Circuit:</b>	Rigid 1/2x0.75 ... 2.5 mm <sup>2</sup>
<b>Connecting Capacity-Control Circuit:</b>	Rigid 1/2x0.75 ... 2.5 mm <sup>2</sup>
<b>Connecting Capacity-Supply Circuit:</b>	Rigid 1/2x0.75 ... 2.5 mm <sup>2</sup>
<b>Tightening Torque:</b>	Main Circuit 1 N·m Supply Circuit 1 N·m Control Circuit 1 N·m
<b>Product Main Type:</b>	PSR16

---

## Certificates and Declarations (Document Number)

<b>Declaration of Conformity - CE:</b>	1SFA1-86
<b>RoHS Information:</b>	1SFC132031D0202

---

## Environmental

<b>Ambient Air Temperature:</b>	Operation -25 ... +60 °C Storage -40 ... +70 °C
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment

---

## Classifications

<b>E-nummer:</b>	3302046
<b>UNSPSC:</b>	39121521

---