

KICK SPACE HEATER

ASKS SERIES

HIDE 'N HEAT

“Hide ‘n heat” is what the ASKS kick space heater by °STELPRO offers. Its redesigned and sleek grille is slimmer than ever, allowing easy installation in narrow spaces like under the kitchen or bathroom cabinets and even into stair risers. Enjoy comfortable forced-air heating from the most discreet fan heater on the market.



ALSO AVAILABLE IN BLACK,
SILICA WHITE AND WHITE



POWER SELECTOR SWITCH

500 W OR 1000 W

EASY INSTALLATION

AESTHETIC GRILLE

SINGLE PIECE, FRAMELESS

IDEAL FOR:

UNDER KITCHEN OR BATHROOM CABINETS,
IN STAIR RISERS

COLORS

- standard: white, silica white, black
- luxurious finish: stainless steel (surcharge)

FINISH

epoxy-polyester powdercoat or stainless steel

MANUFACTURING

- 22-gauge steel cabinet and 16-gauge steel front
- quiet, 50 CFM capacity
- thermal protection with automatic reset
- added protection provided by a fuse-link (must be replaced once activated)

WATTAGE & VOLTAGE

power selector switch (500 W or 1000 W)

ELEMENT

tubular element sheathed with spiral-wound fins for improved heat dissipation

CONTROL

- wall thermostat (not included) – the use of an electronic thermostat is strongly recommended
- built-in thermostat (optional)

INSTALLATION

recessed

ACCESSORIES

PRODUCT	DESCRIPTION
SKST1	built-in single pole thermostat
SKST2	built-in tamper-proof double pole thermostat
SKSR*	extended grille (23 5/8 in. x 3 3/4 in.) allows to cover gaps or imperfections for a renovation project
SKSRSS	extended stainless steel grille (23 5/8 in. x 3 3/4 in.) allows to cover gaps or imperfections for a renovation project

* Add W for white, SW for silica white or BK for black

TECHNICAL SPECIFICATIONS

PRODUCT	POWER		VOLTAGE	THROW DISTANCE	HEAT RISE	WEIGHT
CODE	WATTS	BTU/H	VOLTS	FT.	°F	LB
ASKS1001	500 OR 1000	1706 OR 3413	120	4 (in front)	99	10
ASKS1002	500 OR 1000	1706 OR 3413	240	4 (in front)	99	10

Add W for white, SW for silica white, BK for black or SS for stainless steel