

BA | BELLA™

HIGH-END BASEBOARD



LA DOLCE VITA WITH BELLA

The high-end BELLA baseboard is undoubtedly the most beautiful offered on the market. Its breathtaking design and sturdy aluminum-extruded facade make it the ideal choice for residential and commercial locations. The BELLA is available in two densities: 150 W or 250 W per linear foot.

CLEAN AND HIGH-END FINISH

**EXTREMELY SOLID,
IMPACT AND RUST RESISTANT**
MADE OF EXTRUDED ALUMINUM

**FIT FOR RESIDENTIAL AND
COMMERCIAL ENVIRONMENTS**

TOTALLY QUIET

COLOURS

- **standard:** white, soft white

FINISH

- epoxy-polyester powdercoat

MANUFACTURING

- 22-gauge steel cabinet
- 11-gauge equivalent extruded aluminum with molded and curved end-caps
- discreet air inlet: air enters through the front of the unit and exits from the top
- thermal protection with automatic reset
- full-length wireway

ELEMENT

- single tubular, stainless steel sheathed element with boxed aluminum fins for improved heat dissipation; the element is securely fastened at its centre, floating in nylon sleeves at each end, eliminating expansion and contraction noises

CONTROL

- wall thermostat (not included) – the use of an electronic thermostat is strongly recommended
- built-in mechanical single pole or double pole thermostat, installed in the left or right junction box (optional)
- low voltage relay kit installed in the left or right junction box (optional)
- disconnect switch (optional)

INSTALLATION

- surface mounted
- wiring compartment at both ends of unit

WARRANTY

- five years, *lifetime warranty on the heating element (for original owner)

IDEAL FOR:

kitchen, living room, bedroom, basement, commercial space, office

TECHNICAL SPECIFICATIONS

| DENSITY OF 250 W PER LINEAR FOOT | | DENSITY OF 150 W PER LINEAR FOOT | | VOLTAGE | TOTAL LENGTH* | | WEIGHT | |
|----------------------------------|-----------|----------------------------------|-----------|---------|---------------|----------|--------|------|
| CODE | WATTS | CODE | WATTS | VOLTS | MM | IN. | KG | LB |
| BA0301 | 300 | --- | --- | 120 | 529 | 20 13/16 | 2.3 | 5.1 |
| BA0308 | 300 | --- | --- | 208 | 529 | 20 13/16 | 2.3 | 5.1 |
| BA0302 | 300/225 | --- | --- | 240/208 | 529 | 20 13/16 | 2.3 | 5.1 |
| --- | 300 | --- | --- | 347 | 529 | 20 13/16 | 2.3 | 5.1 |
| --- | 300 | --- | --- | 600 | 529 | 20 13/16 | 2.3 | 5.1 |
| BA0501 | 500 | BAL0301 | 300 | 120 | 732 | 28 13/16 | 3.0 | 6.5 |
| BA0508 | 500 | BAL0308 | 300 | 208 | 732 | 28 13/16 | 3.0 | 6.5 |
| BA0502 | 500/375 | BAL0302 | 300/225 | 240/208 | 732 | 28 13/16 | 3.0 | 6.5 |
| BA0503 | 500 | --- | 300 | 347 | 732 | 28 13/16 | 3.0 | 6.5 |
| --- | 500 | --- | 300 | 600 | 732 | 28 13/16 | 3.0 | 6.5 |
| BA0751 | 750 | BAL0451 | 450 | 120 | 978 | 38 1/2 | 3.6 | 8.0 |
| BA0758 | 750 | BAL0458 | 450 | 208 | 978 | 38 1/2 | 3.6 | 8.0 |
| BA0752 | 750/560 | BAL0452 | 450/340 | 240/208 | 978 | 38 1/2 | 3.6 | 8.0 |
| BA0753 | 750 | BAL0453 | 450 | 347 | 978 | 38 1/2 | 3.6 | 8.0 |
| BA0756 | 750 | --- | 450 | 600 | 978 | 38 1/2 | 3.6 | 8.0 |
| BA1001 | 1000 | BAL0601 | 600 | 120 | 1229 | 48 3/8 | 4.4 | 9.7 |
| BA1008 | 1000 | BAL0608 | 600 | 208 | 1229 | 48 3/8 | 4.4 | 9.7 |
| BA1002 | 1000/750 | BAL0602 | 600/450 | 240/208 | 1229 | 48 3/8 | 4.4 | 9.7 |
| BA1003 | 1000 | BAL0603 | 600 | 347 | 1229 | 48 3/8 | 4.4 | 9.7 |
| BA1006 | 1000 | --- | 600 | 600 | 1229 | 48 3/8 | 4.4 | 9.7 |
| BA1251 | 1250 | BAL0751 | 750 | 120 | 1478 | 58 3/16 | 5.2 | 11.4 |
| BA1258 | 1250 | BAL0758 | 750 | 208 | 1478 | 58 3/16 | 5.2 | 11.4 |
| BA1252 | 1250/940 | BAL0752 | 750/560 | 240/208 | 1478 | 58 3/16 | 5.2 | 11.4 |
| BA1253 | 1250 | BAL0753 | 750 | 347 | 1478 | 58 3/16 | 5.2 | 11.4 |
| BA1256 | 1250 | BAL0756 | 750 | 600 | 1478 | 58 3/16 | 5.2 | 11.4 |
| BA1501 | 1500 | BAL0901 | 900 | 120 | 1707 | 67 3/16 | 6.0 | 13.2 |
| BA1508 | 1500 | BAL0908 | 900 | 208 | 1707 | 67 3/16 | 6.0 | 13.2 |
| BA1502 | 1500/1125 | BAL0902 | 900/675 | 240/208 | 1707 | 67 3/16 | 6.0 | 13.2 |
| BA1503 | 1500 | BAL0903 | 900 | 347 | 1707 | 67 3/16 | 6.0 | 13.2 |
| BA1506 | 1500 | BAL0906 | 900 | 600 | 1707 | 67 3/16 | 6.0 | 13.2 |
| --- | 1750 | BAL1051 | 1050 | 120 | 1953 | 76 7/8 | 6.8 | 15.0 |
| BA1758 | 1750 | BAL1058 | 1050 | 208 | 1953 | 76 7/8 | 6.8 | 15.0 |
| BA1752 | 1750/1310 | BAL1052 | 1050/790 | 240/208 | 1953 | 76 7/8 | 6.8 | 15.0 |
| BA1753 | 1750 | BAL1053 | 1050 | 347 | 1953 | 76 7/8 | 6.8 | 15.0 |
| BA1756 | 1750 | BAL1056 | 1050 | 600 | 1953 | 76 7/8 | 6.8 | 15.0 |
| --- | 2000 | BAL1201 | 1200 | 120 | 2154 | 84 13/16 | 7.7 | 16.9 |
| BA2008 | 2000 | BAL1208 | 1200 | 208 | 2154 | 84 13/16 | 7.7 | 16.9 |
| BA2002 | 2000/1500 | BAL1202 | 1200/900 | 240/208 | 2154 | 84 13/16 | 7.7 | 16.9 |
| BA2003 | 2000 | BAL1203 | 1200 | 347 | 2154 | 84 13/16 | 7.7 | 16.9 |
| BA2006 | 2000 | BAL1206 | 1200 | 600 | 2154 | 84 13/16 | 7.7 | 16.9 |
| --- | 2250 | --- | 1350 | 120 | 2405 | 94 11/16 | 8.6 | 18.8 |
| BA2258 | 2250 | BAL1358 | 1350 | 208 | 2405 | 94 11/16 | 8.6 | 18.8 |
| BA2252 | 2250/1690 | BAL1352 | 1350/1010 | 240/208 | 2405 | 94 11/16 | 8.6 | 18.8 |
| BA2253 | 2250 | BAL1353 | 1350 | 347 | 2405 | 94 11/16 | 8.6 | 18.8 |
| BA2256 | 2250 | BAL1356 | 1350 | 600 | 2405 | 94 11/16 | 8.6 | 18.8 |
| --- | 2500 | --- | 1500 | 120 | 2629 | 103 1/2 | 9.4 | 20.7 |
| BA2508 | 2500 | BAL1508 | 1500 | 208 | 2629 | 103 1/2 | 9.4 | 20.7 |
| BA2502 | 2500/1875 | BAL1502 | 1500/1125 | 240/208 | 2629 | 103 1/2 | 9.4 | 20.7 |
| BA2503 | 2500 | BAL1503 | 1500 | 347 | 2629 | 103 1/2 | 9.4 | 20.7 |
| BA2506 | 2500 | BAL1506 | 1500 | 600 | 2629 | 103 1/2 | 9.4 | 20.7 |

Add W for white, SW for soft white or CA for clear anodized (finish).

* For the wall length, subtract 1/2 in. (13 mm) from the total length.
 --- not available

ACCESSORIES

| PRODUCT | DESCRIPTION |
|--------------|---|
| BA1T1W* | built-in single pole thermostat [120 V-600 V] |
| BA2T1W* | built-in double pole thermostat [120 V-600 V] |
| BARE153* | built-in electronic low voltage relay [15 A @ 120 V-347 V] |
| BARE156* | built-in electronic low voltage relay [6 A @ 600 V] |
| BARE153T* | built-in electronic low voltage relay c/w transformer 24 V [15 A @ 208 V-347 V] |
| BARM240T* | built-in electromechanical relay c/w transformer 24 V [6000 W @ 240 V and 5200 W @ 208 V] |
| BARM347T* | built-in electromechanical relay c/w transformer 24 V [6000 W @ 347 V] |
| BARM347C* | built-in electromechanical relay w/o transformer 24 V [6000 W @ 120 V-347 V] |
| BAR841D1036* | built-in electromechanical low voltage relay w/o transformer 24 V [6000 W @ 600 V] |
| BADIS* | disconnect switch [120 V-480 V] |
| BADIS6* | disconnect switch [600 V] |

Electronic relays can receive a PWM (pulsed width modulation) or digital (on/off) signal.

* Factory installed

* Factory installation is strongly recommended.

TECHNICAL DRAWINGS



