

AFS 4 2C BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

| | |
|------------|---|
| Version | Fuse terminal, PUSH IN, 4 mm ² , 250 V, 6.3 A, black |
| Order No. | 2429860000 |
| Type | AFS 4 2C BK |
| GTIN (EAN) | 4050118439717 |
| Qty. | 50 pc(s). |

AFS 4 2C BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|--------------------------|------------|----------------|------------|
| Depth | 68 mm | Depth (inches) | 2.677 inch |
| Depth including DIN rail | 69 mm | Height | 74 mm |
| Height (inches) | 2.913 inch | Width | 6.1 mm |
| Width (inches) | 0.24 inch | Net weight | 17.5 g |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C | | |

Material data

| | | | |
|---------------------------|-------|--------|-------|
| Material | Wemid | Colour | black |
| UL 94 flammability rating | V-0 | | |

Rating data IECEx/ATEX

| | | | |
|--------------------------------|-------------------|---------------------------------|-------------------|
| Certificate No. (ATEX) | TUEV17ATEX8064U | Certificate No. (IECEX) | IECEXTUR17.0030U |
| Max. voltage (ATEX) | 250 V | Current (ATEX) | 6.3 A |
| Wire cross section max. (ATEX) | 4 mm ² | Max. voltage (IECEX) | 250 V |
| Current (IECEX) | 6.3 A | Wire cross section max. (IECEX) | 4 mm ² |
| Marking EN 60079-7 | Ex ec II C Gc | Ex 2014/34/EU label | II 3 G D |

System specifications

| | | | |
|-------------------------------|-------|-------------------------------------|----|
| End cover plate required | Yes | Number of potentials | 1 |
| Number of levels | 1 | Number of clamping points per level | 2 |
| Number of potentials per tier | 1 | PE connection | No |
| Rail | TS 35 | N-function | No |
| PE function | No | PEN function | No |

Additional technical data

| | | | |
|---------------------|-------|-------------------|---------|
| Installation advice | Rail | Open sides | right |
| Snap-on | No | Type of fixing | Snap-on |
| Type of mounting | TS 35 | With snap-in pegs | No |

CSA rating data

| | | | |
|-------------------------------|-----------------|-------------------------------|--------|
| Certificate No. (CSA) | 200039-70089609 | Current size B (CSA) | 10 A |
| Current size C (CSA) | 10 A | Current size D (CSA) | 10 A |
| Voltage size B (CSA) | 300 V | Voltage size C (CSA) | 150 V |
| Voltage size D (CSA) | 300 V | Wire cross section max. (CSA) | 10 AWG |
| Wire cross section min. (CSA) | 26 AWG | | |

Conductors for clamping (rated connection)

| | |
|--|----------------------|
| Blade size | 0.6 x 3.5 mm |
| Clamping range, max. | 4 mm ² |
| Clamping range, min. | 0.14 mm ² |
| Connection cross-section, stranded, max. | 4 mm ² |
| Connection cross-section, stranded, min. | 0.5 mm ² |
| Connection direction | top |
| Gauge to IEC 60947-1 | A4 |

Creation date February 16, 2022 11:07:36 AM CET

Catalogue status 11.02.2022 / We reserve the right to make technical changes.

AFS 4 2C BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | | | |
|---|--|---------|---------------------|
| Number of connections | 2 | | |
| Stripping length | 12 mm | | |
| Tube length for twin wire-end ferrule | Tube length | min. | 8 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | min. | 0.5 mm ² |
| | | max. | 1.5 mm ² |
| Tube length for wire-end ferrule with plastic collar DIN 46228/4 | Tube length | min. | 6 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | min. | 0.5 mm ² |
| | | max. | 1 mm ² |
| | Tube length | min. | 8 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | min. | 1.5 mm ² |
| | | max. | 2.5 mm ² |
| | Tube length | min. | 10 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | nominal | 4 mm ² |
| | | | |
| Tube length for wire-end ferrule without plastic collar DIN 46228/1 | Cross-section for conductor connection | min. | 0.5 mm ² |
| | | max. | 1 mm ² |
| | Tube length | min. | 6 mm |
| | | max. | 10 mm |
| | Cross-section for conductor connection | min. | 1.5 mm ² |
| | | max. | 2.5 mm ² |
| | Tube length | min. | 7 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | nominal | 4 mm ² |
| | | | |
| | Tube length | min. | 9 mm |
| | | max. | 15 mm |
| Twin wire-end ferrules, max. | 1.5 mm ² | | |
| Twin wire-end ferrules, min. | 0.5 mm ² | | |
| Type of connection | PUSH IN | | |
| Wire connection cross section AWG, max. | AWG 12 | | |
| Wire connection cross section AWG, min. | AWG 26 | | |
| Wire connection cross section, finely stranded, max. | 4 mm ² | | |
| Wire connection cross section, finely stranded, min. | 0.5 mm ² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 4 mm ² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm ² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 4 mm ² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm ² | | |
| Wire connection cross-section, solid core, max. | 4 mm ² | | |
| Wire connection cross-section, solid core, min. | 0.5 mm ² | | |