



Fuse terminal with screw terminal Terminal size 4.0 mm² Terminal width 6.2 mm Color black fuse 5x 20 mm

Model		
product brand name	SETRON	
General technical data		
terminal contact spacing	6 mm	
Supply voltage		
operating voltage / rated value	500 V	
Protection class		
combustibility class according to UL 94	V0	
Main circuit		
operational current / rated value	6 A	
Appearance		
color	black	
Product details		
product component / required / end cover plate	No	
Number		
number of terminal levels	1	
Connections		
stripped length	9 mm	
connectable conductor cross-section / solid		
• minimum	0.14 mm ²	
• maximum	6 mm ²	
connectable conductor cross-section / finely stranded		
• with core end processing / minimum	0.1 mm ²	
• with core end processing / maximum	4 mm ²	
type of connection		
• 1	screw-type terminal	
• 2	screw-type terminal	
position / of the terminal	lateral	
Mechanical Design		
height / with lowest-profile installation	73 mm	
length	58 mm	
fastening method	DIN rail 35 mm	
material / of the insulating body	Thermoplast	
Environmental conditions		
ambient temperature / during operation		
• minimum	-25 °C	
• maximum	55 °C	
General Product Approval		
	Declaration of	other

[Confirmation](#)[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WH1000-1GG08>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8WH1000-1GG08>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8WH1000-1GG08

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



