Featured Models

Non-Metallic, Non-Fusible Disconnects, 1-phase, 120/240V

Non-fusible disconnect pullers are removable or reinstalled in the OFF position for user safety during equipment maintenance.

Model Number	Amp	Horsepower Rating	Wire Range	Cabinet Size	Unit Wt.	Std. Pkg.	UL
P065P1	60	10	D	5 x 7	2	6	V 1
P065P	60	10	D	6 x 8			'



P065P1

Non-Metallic, Fusible Disconnects, 1-phase, 120/240V

Fusible disconnects are available in 30 and 60 Amp models. Pullers are removable or reinstallable in the OFF position for user safety during equipment maintenance. The P065F UL Listing includes the ability to field replace the 60 Amp puller with 30 Amp puller (FR352) for installation flexibility. Listed for use as service entrance.

Model Number	Amp	Horsepower Rating	Wire Range	Cabinet Size	Unit Wt.	Std. Pkg.	UL
P035F	30	3	D	6 x 8	2	6	V1
P065F	60	10	D	6 x 8		0	'



P035F

Metallic, Non-Fusible Disconnects, 1-phase or 3-phase

Non-fusible disconnect pullers are removable or reinstalled in the OFF position for user safety during equipment maintenance.

Model Number	Amp	Horsepower Rating	Wire Range	ge Cabinet Size		Std. Pkg.	UL		
Phase 1 – 120/240V									
U065P	60	10	D	5 x 7	3	6	Y ¹		
Phase 3 – 240V	Phase 3 – 240V								
U0653P	60	7.5-15	D	6 x 14	8.5	4	Y ¹		



U065P

Metallic, Fusible Disconnects, 1-phase or 3-phase

Fusible disconnects are available in 30 and 60 Amp models. Pullers are removable or reinstallable in the OFF position for user safety during equipment maintenance. Listed for use as service entrance.

Model Number	Amp	Horsepower Rating			Unit Wt.	Std. Pkg.	UL
Phase 1 - 120/240V							
U035F2	30	3	D	5 x 7	2.5	6	V1
U065F1	60	10	D	5 x 9	3.5	U	, i
Phase 3 – 240V					•		
U0353F	30	3-7.5	D	6 x 14	8.5	4	V1
U0653F	60	7.5-15	D	6 x 14	0.5	4	ı



U065F1

Non-Automatic Disconnect Switch, 1-phase, 120/240V

Model Number	Amp	Horsepower Rating	Wire Range	Cabinet Size	Unit Wt.	Std. Pkg.	UL
Metallic							
U065NA1	60	10	D	5 x 7	2.5	6	Y ¹
Non-Metallic							
P065NA1	60	10	D	5 x 7	2	6	Y ¹



U065NA1

Heat Pump, Fusible Disconnects, 1-phase, 120/240V

Multiple disconnect devices are offered for heat pump applications that require individual disconnects for the heating and cooling cycles. All pullers are removable or reinstalled in the OFF position for user safety during equipment maintenance. Their UL Listing includes the ability to field replace the 60 Amp puller in the left fuse block with a 30 Amp puller (FH352) for installation flexibility but prohibits the interchageability of pullers between fuse blocks to ensure the proper fuse/puller combination is always reinstalled in the proper fuse block.

Model Number	Amp	Horsepower	Neutral Bar	Wire Range	Cabinet Size	Unit	Std.	UL
Fusible	Amp	Rating	iteatiai Bai	Wile Hallge	Oubillet Gize	Wt.	Pkg.	0_
U045F	90	10	NU100B2		9 x 17	13.5	1	V
U610F	100	10	11010002	'	3 X 17	10.0	'	'



U610F

Evaporation Cooler, Fusible Disconnects, 1-phase, 120/240V

Evaporation cooler applications not only require fusing but switching or receptacle function depending on equipment type and local codes. Two models are offered to meet these varied evaporation cooler applications.

Model Number Fusible	Receptacles	Circuit Protection	Amp	Wire Range	Cabinet Size	Unit Wt.	Std. Pkg.	UL
U22OH	DPST, SPST Switch	(2) FH1	20	AR	5 x 7	4.5	4	N
U261F	14-20R, 5-20R2	(3) FH1	40	Е	6 x 9	6	4	Y ¹



Disconnects, Ground Fault, 1-phase, 120/240V

Combination AC disconnects are designed for use as an AC unit, an outdoor GFCI or an in-use weather-proof cover for an outdoor GFCI receptacle. The three models offered meet NEC requirements.

Model Number	Receptacles	Amp	Horsepower Rating	Wire Range	Cabinet Size	Unit Wt.	Std. Pkg.	UL
U065P010	5-15R2GFI					4.3	6	
U065NA1010	5-15R2GFI	60	10	D	5 x 7	4	6	Y ¹
U065PC2	5-20R2					4.3	4	



Exterior Mounting Bracket STC1

Exterior Mounting Bracket for single-phase AC & AC/GFCI disconnects in aluminum, vinyl siding and stucco applications. Order quantity in multiples of six. Mounting hardware for fastening AC disconnect to STC1 included.



Technical Data

		lacement Pa	rts	Cabinet	Enclosure	Cal	oinet Dimer	nsions (incl	nes)	Knockout
Model Number	Complete Block and Puller	Fuse Block Only	Puller Only	Size	Style	Height (A)	Width (B)	Depth (C)	Depth (D)	Figure
P035F	FR39	_	FR352	6 x 8	С	8	5-3/4	3-1/8	_	1
P065F	FR69	_	FH682	6 x 8	С	8	5-3/4	3-1/8	_	1
P065NA1	_	_	_	5 x 7	D	7-1/4	5	2-1/8	2-3/4	2
P065P	_	NF65	NF652	6 x 8	D	8	6	5-3/4	2-3/4	2
P065P1	_	NF65	NF652	5 x 7	D	7	5	2-1/8	2-3/4	2
U035F2	FR35R	_	FR352R	5 x 7	А	7	5	2-1/8	2-3/4	2
U0353F	265A6035G27	_	265A6035G27	6 x 14	В	14-3/8	7-1/4	5-3/16	_	3
U045F	FR35XFR67	_	FR352, FH682	9 x 17	В	17-3/8	9-3/4	5-3/16	_	4
U0653F	265A6036G69	_	265A6036G69	6 x 14	В	14-3/8	7-1/4	5-3/16	_	3
U0653P	265A6036G73	_	265A6036G73	6 x 14	В	14-3/8	7-1/4	5-3/16	_	3
U065F1	FR65	_	FH682	5 x 9	А	9	5	2-1/8	2-3/4	2
U065NA1	_	_	_	5 x 7	D	7	5	2-1/8	2-3/4	2
U065NA1010	_	_	_	5 x 7	D	7	5	3-5/8	5-3/16	2
U065P	_	NF65	NF652	5 x 7	А	7-1/4	5	2-1/8	2-3/4	2
U065P010	_	NF65	NF652	5 x 7	D	7	5	3-5/8	5-3/16	2
U065PC2	_	NF65	NF652	5 x 7	D	7	5	2-1/8	2-3/4	2
U220H	_	FH1	_	5 x 7	В	7-1/8	5-3/4	5-3/16	_	5
U261F	_	FH1	_	6 x 9	В	9-1/8	7-1/4	5-3/16	_	3
U610F	FR67X2	_	FH682	9 x 17	В	17-3/8	9-3/4	5-3/16	_	4

Cabinet Dimensions

