



LED PAR38

10PAR38/LED/930/F40/DIM/GULW/T20 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data


General information	
Cap-Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Light technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	40 °
Luminous Flux (Nom)	900 lm
Luminous Intensity (Nom)	1900 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	10 W
Lamp Current (Nom)	97 mA
Wattage Equivalent	90 W
Starting Time (Nom)	0.5 s

Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and dimming	
Dimmable	Only with specific dimmers
Mechanical and housing	
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]
Approval and application	
Suitable For Accent Lighting	Yes
Product data	
Order product name	10PAR38/LED/930/F40/DIM/GULW/T20 6/1FB
EAN/UPC - Product	046677567903
Order code	567909
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929003029104

LED PAR38

Net Weight (Piece) 0.385 kg

Dimensional drawing




10PAR38/LED/930/F40/DIM/GULW/T20 6/1FB


Product

10PAR38/LED/930/F40/DIM/GULW/T20 6/1FB


Photometric data



LEDspots N DIM 10W PAR38 E26 930 40D-POC



LEDspots N DIM 10W PAR38 E26 930 40D-LDD



Technical Information 11


LEDspots N DIM 10W PAR38 E26 930 40D 1-ADL

LED PAR38

Lifetime



LEDspots LED 25K



LEDspots LMP 25K

