

Levels & Measuring Tools

Quick, easy and accurate measurements can mean the difference between a job well done and one that misses the mark. Klein offers a variety of levels and other measuring devices that will help you measure up to the task.

For Professionals...
Since 1857™



Levels

Features:

Large, high visibility vials are easy to read.

Handy V-grooved edge for pipe and conduit work.

Extruded, die-cast aluminum frame features a convenient built-in hang hole.

Precision edges for accuracy.

Laser-etched rule and markings for high visibility readings.

Powerful rare earth magnets firmly hold the level to ferrous metals.



Magnetic Torpedo Level

Additional Features:

- Lightweight, precision-made for durability and performance.
- Convenient 9" length for use in tight spaces.
- Three acrylic vials – plumb, level and 45° provide the necessary jobsite measurements.
- Magnetized strip on bottom.



931-9RE

Cat. No.	Overall Length	Weight
930-9	9" (229 mm)	.25 lbs. (0.12 kg)

Rare Earth Magnetic Torpedo Level

Additional Features:

- Powerful rare earth magnets, 10x stronger than strip magnets, hold firmly to iron and steel surfaces.
- Three acrylic vials – plumb, level and 45° provide the necessary jobsite measurements.
- Top read level window simplifies viewing in tight areas.



930-9

Cat. No.	Overall Length	Weight
931-9RE	9" (229 mm)	.42 lbs. (0.19 kg)

9" Torpedo Level

Additional Features:

- Easy to read vials set for measurements at 0, 30, 45 and 90 degrees.
- Machined billet aluminum design.



932-9RE-SEN

Cat. No.	Overall Length	Weight
932-9RE-SEN	9" (229 mm)	.46 lbs. (0.21 kg)

9" Torpedo Lighted Level

Additional Features:

- Lights up for maximum visibility.
- 3-minute auto shut-off saves battery life.
- Includes 2 AAA batteries.
- Water and impact resistant.
- Easy to read vials set for measurements at 0, 45 and 90 degrees.
- Machined billet aluminum design.



9330RE

Cat. No.	Overall Length	Weight
9330RE	9" (229 mm)	.525 lbs. (0.24 kg)

All dimensions are in inches and (millimeters) unless otherwise specified.



www.kleintools.com

See page 310 for additional information on warnings.



Levels

Accu-Bend™ Level

Additional Features:

- Ensures precise 90° bends.
- Eliminates dog legs in conduit bends.
- 3 points of contact for superior hold to conduit.
- Relaxed V-Groove accepts up to 1" conduit.
- Solid aluminium frame for extreme durability.



9317RE



⚠️WARNING: 9317RE brass bolt contains lead, a chemical known to the State of California to cause cancer, and birth defects or other reproductive harm. Wash hands after handling.

Cat. No.	Overall Length	Weight
9317RE	2-1/2" (64 mm)	.162 lbs (0.07 kg)

Tape Measures

Features:

Clean corner access for flush edge measurements.

Steel belt clip for convenience.

Non-marring foot slides for a clean work surface.



Non-slip rubber case for comfort.

Non-flip case with nylon coated blades that resist abrasion and wear.

True zero feature for accurate inside and outside measuring.

Large rare earth magnetic end hooks for 5x the strength. Screws securely hold magnets in place.

⚠️WARNING: Protect hands when cleaning magnetic tip. Use gloves or cloth.

⚠️WARNING: Avoid magnetic contact with sensitive electronic or computer equipment.

⚠️WARNING: To avoid personal injury and damage to this tool, do not allow the tape blade to retract into case at full speed.

⚠️WARNING: Do NOT open case. Spring motor is under tension, and opening case may cause injury.

Tape Measures – Magnetic



Rare earth magnets are 5x stronger!

93225

Additional Features:

- First 11" (279 mm) has oversized, bold numbers (except 93275).
- Easy read fractional scale (except 93275).
- Double-sided rule for measurement while using against wall, ceiling or conduit.
- Horizontal and vertical standout for easy one person measurements.
- Shock and impact resistant case.

Cat. No.	Blade Length	Hook	Weight
93116	16' (5 m)	single	.63 lbs. (0.29 kg)
93125	25' (7.5 m)	single	.91 lbs. (0.41 kg)
93225	25' (7.5 m)	double	.94 lbs. (0.43 kg)
93275*	7.5 m (25')	double	.94 lbs. (0.43 kg)
93430	30' (9 m)	double	1.2 lbs. (0.54 kg)

*Note: 93275 features both centimeters and inches on both sides of blade.

All dimensions are in inches and (millimeters) unless otherwise specified.



Tape Measures

Tape Measure – 25 Feet



93025

Additional Features:

- Oversized, bold blade numbers on first 11" (279 mm) for easy reading.
- 16" stud markings and 19.2" truss markings.
- Non-magnetic single hook.
- Rubberized lock button for comfort.
- Impact absorbing case.

Cat. No.	Blade Length	Hook	Weight
93025	25' (7.5 m)	single	.84 lbs. (0.38 kg)

Tape Measures – Steel with High-Visibility Case



928-25HV

- High-visibility, high-impact orange case makes it easy to find in a tool box, pouch and on the jobsite.
- 16" stud markings and 19.2" truss markings.



Cat. No.	Blade Length	Width	Weight
928-25HV	25' (7.5 m)	1" (25 mm)	1.00 lbs. (0.45 kg)

Tape Measure Holders

- Klein offers a complete selection of leather or nylon Tape Holders and Pouches.



5195



5707

Tape Measure	Cat No.	Description
93116, 928-16HV	5194	small leather pouch
	5707	nylon tape measure clip/holder
93025, 93125	5195	medium leather pouch
	5707	nylon tape measure clip/holder
93225, 93275, 928-25HV	5196	large leather pouch
	5707	nylon tape measure clip/holder
93430	5712	nylon pouch



All dimensions are in inches and (millimeters) unless otherwise specified.



Folding Rules

Wood Folding Rules

- Strong, 6' (183 cm) long hardwood rules with clear abrasion-resistant coating.
- Black markings on yellow, with red stud center markings every 16 inches.
- Measurements are marked on both sides and both edges, and graduated to 1/16th inch.
- Riveted lock joints are designed for long wear and maintained accuracy.
- Extension slide moves under friction in a T-slot with stops at each end. (Cat. No. 905-6)




910-6

Cat. No.	Reading	Length	Weight
900-6	inside	6' (183 cm)	.33 lbs. (0.15 kg)
901-6	outside	6' (183 cm)	.33 lbs. (0.15 kg)

Cat. No.	Reading	Length	Weight
6-Ft. Folding Rule — with Extension			
905-6	outside	6' (183 cm)	.33 lbs. (0.15 kg)

Non-Conductive Fiberglass Folding Rules

- Constructed of tough nylon, reinforced with glass fibers for added durability, and resistance to weather, abrasion and most chemicals.
- Positive locking joints and stainless steel spring hinges for added strength.
- Measurements are marked on both sides and both edges, graduated to 1/16th inch.
- Black markings on yellow, with red stud center markings every 16 inches.
- Engraved graduations on both sides.



901-6

Cat. No.	Reading	Length	Weight
910-6	inside	6' (183 cm)	.33 lbs. (0.15 kg)
911-6	outside	6' (183 cm)	.33 lbs. (0.15 kg)

Fiberglass Tapes

Woven Fiberglass Tape – Case

- Woven fiberglass tape with moisture-proof coating of polyvinyl chloride assures durability and protects against oil or chemicals.
- Can be immersed in water without adverse effects.
- All metal parts are nickel-plated for protection against rust.
- End-hooks are permanently attached to reinforced strip.
- Case and reel are ruggedly built yet lightweight and comfortable to use.
- Tape line graduated in feet and inches to 8ths.
- Black graduating numbers and red foot markings on yellow background.
- Protective carrying case encloses tape completely.
- Tape ring tucks neatly into case opening for storage.



946-100

Cat. No.	Length	Width	Weight
946-50	50' (15 m)	1/2" (13 mm)	.80 lbs. (0.36 kg)
946-100	100' (30 m)	1/2" (13 mm)	1.20 lbs. (0.54 kg)

Woven Fiberglass Tape – Open-Reel

- Woven fiberglass tape with moisture-proof coating of polyvinyl chloride assures durability and protects against oil or chemicals.
- Can be immersed in water without adverse effects.
- Black figures on a yellow background are easy to read.
- All metal parts are nickel-plated for protection against rust.
- End-hooks are permanently attached to a reinforced strip.
- Case and reel are ruggedly built, yet lightweight and comfortable to use.
- Tape line is graduated in feet and inches to 8ths.
- Graduations and numbers are black; foot markings are red.
- Contained in an open reel and is easy to handle and rewind.



946-150

Cat. No.	Length	Width	Weight
946-150	150' (46 m)	1/2" (13 mm)	1.70 lbs. (0.77 kg)

All dimensions are in inches and (millimeters) unless otherwise specified.

