

Product data sheet

Specifications



APC Back-UPS Pro 1350S, 1350VA, 120V, Sinewave, AVR, LCD, 2 USB charging ports, 10 NEMA outlets (4 surge)

BR1350MS

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Rated power in W	810 W
Rated power in VA	1350 VA
Plug standard	NEMA 5-15P
Nb of power socket outlets	6 NEMA 5-15R 4 NEMA 5-15R surge
Cable length	1.83 m
Number of cables	1
Battery type	Lead-acid battery

General

Provided equipment	coaxial cable user manual USB cable
Product web sub-family	Gaming performance
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

Height	26 cm
Width	10 cm
Depth	36.8 cm
Net weight	11.7 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable

Two post mountable	0
USB compatible	No

Input

Network frequency	60 Hz +/- 3 Hz
Input voltage limits	88...147 V
Maximum input current	12 A
Switching current capacity	15 A

Output

Maximum configurable power in W	810 W
Output frequency	60 Hz +/- 3 Hz sync to mains
UPS type	Line interactive
Wave type	Sine wave
Maximum configurable power in VA	1350 VA
Transfer time	8 ms typical : 10 ms maximum

Conformance

Product certifications	ENERGY STAR V2.0 (USA) NOM TUV C-US certified
Standards	FCC part 15 class B
Equipment protection policy	Lifetime : \$500000

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...40 °C
Storage Relative Humidity	0...95 % Non-condensing
Storage altitude	0.00...3048.00 m
Acoustic level	45 dBA

Batteries & Runtime

Number of battery filled slots	1
Number of battery free slots	0
Battery recharge time	16 h
Number of battery replacement quantity	2
Battery charger power	10 W rated
Battery power in VAH	168 VAh capacity 168 VAh runtime
Battery life	3...5 year(s)
Extended runtime	0

Communications & Management

Control panel	Multifunction LCD status and control console
Alarm	Alarm when on battery : distinctive low battery alarm


Surge Protection and Filtering

Surge energy rate	1080 J
Noise suppression	Full time multi-pole noise filtering : 5% of IEEE surge let-through : zero clamping response time: instantaneous
Data line protection	RJ45 10/100/1000 Base-T Ethernet protection Coaxial video/cable protection

Packing Units

Package 1 Weight	13.3 kg
Package 1 Height	35.87 cm
Package 1 width	22.3 cm
Package 1 Length	48.2 cm
SCC14	10731304335396
Number of Units in Package 2	1
Package 2 Weight	13.30 kg
Package 2 Height	482.60 mm
Package 2 width	228.60 mm
Package 2 Length	355.60 mm
Number of Units in Package 3	16

Offer Sustainability

ENERGY STAR®	ENERGY STAR UPS V2.0 (USA) 
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------