



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Input voltage	120 V
Output voltage	120 V
Rated power in W	400 W
Rated power in VA	500 VA
Plug standard	NEMA 5-15P
Nb of power socket outlets	4 NEMA 5-15R
Number of rack unit	1U
Battery type	Li-Ion (Lithium-Ion)
Provided equipment	CD with software Documentation CD Installation guide Rack mounting support rails USB cable

General

Number of power module filled slots	0
Number of power module free slots	0
Additional specification	Lithium-Ion
Redundant	No

Physical

Colour	Black with silver front bezel
Height	4.4 Cm
Width	43.2 Cm
Depth	23.2 Cm
Net weight	4.22 Kg
Mounting support	Floor Wall
Mounting preference	No preference
Mounting mode	Rack-mounted
Two post mountable	1
USB compatible	Yes

Input

Input voltage limits	92...139 V
Network frequency	47...63 Hz

Output

Maximum configurable power in VA	500 VA
Maximum configurable power in W	400 W
Transfer time	6 ms typical : 10 ms maximum
UPS type	Line interactive
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product certifications	CULus NOM
Equipment protection policy	Lifetime : \$150000
Standards	CSA C22.2 No 107.3 FCC part 15 class A UL 1778 UL 1973

Environmental

Acoustic level	45 dBA
Operating altitude	0...6561 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...14999.82 M
Relative humidity	10...90 % non-condensing
Storage Relative Humidity	Non-condensing 10...90 %

Batteries & Runtime

Extended runtime	0
Battery design life	5...10 Year(S)
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 H
Battery life	8...10 Year(S)
Battery power in VAh	30 VAh runtime
Battery charger power	10 W rated

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	LED Status display with on line : on battery
Free slots	0

Surge Protection and Filtering

Surge energy rate	680 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Package 1 Weight	6.49 Kg
Package 1 Height	16.8 Cm
Package 1 width	59 Cm
Package 1 Length	33.7 Cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Product Life Status : **Commercialised**