

# Product data sheet

## Characteristics

# SMT1500RM2UNC

APC Smart-UPS, Line Interactive, 1500VA,  
Rackmount 2U, 120V, 6x NEMA 5-15R outlets,  
Network Card, AVR, LCD



### Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable run-time. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock

### Main

Input voltage	120 V
Output voltage	120 V
Rated power in W	1000 W
Rated power in VA	1440 VA
Plug standard	NEMA 5-15P
Nb of power socket outlets	6 NEMA 5-15R
Number of rack unit	2U
Cable length	2.44 M
Battery type	Lead-acid battery
Provided equipment	CD with software Documentation CD Installation guide Rack mounting support rails USB cable

### General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No

### Physical

Colour	Black
Height	8.9 Cm
Width	43.2 Cm
Depth	45.7 Cm
Net weight	28.67 Kg
Mounting preference	No preference
Mounting mode	Rack-mounted

Two post mountable	0
USB compatible	No

## Input

Input voltage limits	82...144 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing

## Output

Harmonic distortion	Less than 5 %
Maximum configurable power in VA	1440 VA
Maximum configurable power in W	1000 W
Transfer time	4 ms typical : 8 ms maximum
UPS type	Line interactive
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

## Conformance

Product certifications	CSA
Standards	FCC part 15 class A UL 1778

## Environmental

Acoustic level	46 dBA
Heat dissipation	90 Btu/H
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 M
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

## Batteries & Runtime

Extended runtime	0
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 H
Number of battery replacement quantity	1
Battery life	4...6 Year(S)
Battery power in VAH	432 VAh runtime
Battery charger power	144 W rated

## Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	Multifunction LCD status and control console
Emergency power off	Optional
Free slots	0
Preinstalled device	Network management card 2 with environmental monitoring

## Surge Protection and Filtering

Surge energy rate	459 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

## Packing Units

Package 1 Weight	31.93 Kg
Package 1 Height	25.1 Cm
Package 1 width	59.4 Cm
Package 1 Length	60.3 Cm
Number of Units in Package 3	8

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and-lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	-----------------------------------------------------------------------

Product Life Status : **Commercialised**