THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

	STUD	SIZE	DIMENSIONS in. [mm]					
PANDUIT PART #	ENGLISH	METRIC	L ± .03 [0,8]	W ± .01 [0,3]	C ± .02 [0,5]	M± .03 [0,8]	H± .01 [0,3]	
PMV6-3R*		М3	1.02 [26,0]	.23 [5,8]	.31 [7,8]	.89 [22,61]	.13 [3,3]	
PV10-6R	#6	M3,5	1.05 [26,7]	.31 [7,9]	.31 [7,9]	.89 [22,6]	.15 [3,8]	
PV10-8R	#8	M4	1.05 [26,7]	.31 [7,9]	.31 [7,9]	.89 [22,6]	.17 [4,3]	
PV10-10R	#10	 M5	1.05 [26,7] 1.07 [27,1]	.31 [7,9] .37 [9,5]	.31 [7,9]	.89 [22,6] .89 [22,61]	.20 [5,1] .21 [5,3]	
PMV6-5R*					.31 [7,8]			
PV10-14R	1/4"	M6	1.23 [31,2]	.52 [13,2]	.38 [9,7]	.97 [24,6]	.27 [6,9]	
PV10-56R	5/16"	M8	1.23 [31,2]	.52 [13,2]	.38 [9,7]	.97 [24,6]	.33 [8,4]	
PV10-38R	3/8"		1.31 [33,3]	.58 [14,7]	.41 [10,4]	1.02 [25,9]	.39 [9,9]	
PV10-12R	1/2"		1.46 [37,1]	.72 [18,3]	.53 [13,5]	1.10 [27,9]	.52 [13,2]	


* NOT UL LISTED

NOTES:

В

- 1. USED FOR:
 - A. #12-10 AWG [4,0-6,0 mm²] STRANDED COPPER WIRE B. 221°F [105°C] MAX. OPERATING TEMPERATURE

 - C. 600V. MAX. BLDG WIRE
- (1000 V. MAX. IN SIGNS, FIXTURES & LUMINAIRES)
 2. INSTALLATION TOOLS PANDUIT APPROVED:
- - A. UL APPROVED: CT-100A, CT-600-A (CT-550CH)
 - CT-1550, CT-1551, CT-2500(CT-2550CH)
 - B. PANDUIT APPROVED: CT-160, CT-260, CT-460
- 3. WIRE STRIP LENGTH: 5/16 1/32 [7,9 10,8]
- 4. MATERIAL:
 - A. STAMPING: .04" [1,0] THK COPPER, TIN PLATED B. HOUSING: VINYL, YELLOW
- 5. SEE www.panduit.com FOR PACKAGE QUANTITIES
 - INDICATED BY PART NUMBER SUFFIX
- 6. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



В



LISTED CERTIFIED LR31212 587H E52164

	<u> </u>							The same	1	
A								RING TERMINALS, 2-PC VINYL INSULATED, #12-10		
								CUSTOMER DRAWING		
								N41187BA/09		
								N4118/BA/09 DATASET FILE NAME N41187BA_DC/09A HANDUIT		
	09	04/23/20	HPR	CLN	JADE	REV NUMBER CORRECTED FROM 7 TO 8	078745	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		
04/12	08	06.07.12	BDK	LCA	VMB	REVISED PACKAGING NOTE. REVISED "USED FOR" NOTE. REMOVED PACKAGING CODE FROM CHART. ADDED PMV6-3R AND PMV6-5R TO CHART. ADDED INSTALLATION TOOL NOTE.	A 41187	.x ± .1 [2.54] .xx ± .005 [.13] SEE NOTES .xx ± .01 [.25] ANGLES ± 5 * THIRD ANGLE PROJECTION A41187		
10100	REV	DATE	BY	СНК	APR	DESCRIPTION	ECN	FES - LCA N.T.S. SHEET 1 OF 1		